


FEMALE NON CRIMP CONTACTS



PERFORMANCE CHARACTERISTICS :

Current rating : 13 Amp
 Contact resistance : 3m Ohm
 Operating voltage : 750 V RMS
 Contact retention in body : 110 N Mini.
 Individual insertion force : 3,5 N
 Individual withdrawal force : 0,55 N mini

MATERIAL

Contact body : Brass
 * Plating : J-K-N-L-M-D70-D28 = Gold Flash over Nickel
 T = 3 - 5µ Tin over Nickel
 Retaining spring : Beryllium copper not plated
 Inner contact spring : Beryllium copper
 * Plating : J = Gold Flash over Nickel
 K = 0,4µ Gold over Nickel
 N = 0,75µ Gold over Nickel
 L = 1,10µ Gold over Nickel
 M = 1,75µ Gold over Nickel
 T = 3 - 5µ Tin over Nickel
 D70 = Gold flash over Nickel
 D28 = 0,75µ Gold over Nickel

NOTES

- 1/ Contacts suitable for : SMS - MSG - MB - MBG
MSM - UTO - UTS - UTG - UTP
- 2/ Packaging : RC---M--* : 50 pcs Bulk packaging
RC--M--E25* : 25 pcs Bulk packaging
RC--M---*1000 : 1000 pcs Bulk packaging
- 3/ Marking : No colour marking
- 4/ Female contact accept Dia. 1,6 mm male contacts
- 5/ To know the length of the dip solder or wrap pin on the connectors:
see customer drawing of the concerned connector.

FEMALE NON CRIMP CONTACTS

PART NUMBER	TYPE	FIG	WIRE SIZE		POST CROSS SECTION	ANTI-ROTATING BUSHING CAT. NR	EXTRACTION TOOL
			AWG	MM ²			
RC16SE4*	HANDSOLDER	1	20 - 16	0,52 - 1,50	∅ 1,7	---	RX2025GE1 AND RX2025GE2
RC20M12G4*	MINI-WRAP	2	30 - 28 SOLID	0,05 - 0,08	0,636 x 0,635	J1661	
RCM207CGE00*	MAXI-WRAP	3	26 - 20 SOLID	0,13 - 0,50	1 x 1	J1661CGE00	
RC20M12E8*	DIPSOLDER	4	---	---	∅ 0,9	---	
RC20M12E83*	DIPSOLDER	5	---	---	∅ 0,9	---	
RC20M12E84*	DIPSOLDER	6	---	---	∅ 0,9	---	
RC20M12E86*	DIPSOLDER	7	---	---	∅ 0,9	---	
RC20M12E87*	DIPSOLDER	8	---	---	∅ 0,9	---	

* Plating identification

P/N : SEE TABLE

b		29/01/2014		- Ajout de la note "5"		23370	
ISS		DATE		Latest modification - by:		FOUBERT E.	
DESIGNED BY:		CHARLOT MA		DATE: 20/06/12		CUSTOMER DRAWING	
TITLE		TRIM-TRIO SOCKET CONTACT SIZE 16 SPECIFIC					
		RC-----					
Scale		5/1		General linear Tolerances: ± 0,2		NPRDS / PROJECT RC	
SOURIAU		WWW.SOURIAU.COM				This document is the property of SOURIAU It must not be reproduced or communicated without permission	
FORMAT		A2				SOURIAU DRG N° BSC201448005	
						SHEET 1/1	

NOT EXPORT CONTROLLED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Souriau:

[RC24M9D28](#) [RC16M23D28](#) [RFD26L-1D28](#) [RM16M23GE1K](#) [RC24M9E25K](#) [RFM26W-1D28](#)