

**MEHA KP RT M-D-SPX****Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



- Flexible and solid wire with PVC, Teflon (PTFE) and silicone insulation
- No damage to the wire thanks to specially shaped blade
- No splicing of individual wires
- Blade inserts are easy to replace
- All inserts fit one housing
- Guide bars in the blade cassettes facilitate correct positioning of the wire in the tool

**General ordering data**

Version	Accessories, Set of cutters
Order No.	<a href="#">900361000</a>
Type	MEHA KP RT M-D-SPX
GTIN (EAN)	4008190058272
Qty.	1 pc(s).

## MEHA KP RT M-D-SPX

Weidmüller Interfaces GmbH &amp; Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

[info@weidmueller.com](mailto:info@weidmueller.com)[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Dimensions and weights

Depth	16 mm	Depth (inches)	0.63 inch
Height	11.5 mm	Height (inches)	0.453 inch
Width	26 mm	Width (inches)	1.024 inch
Net weight	3.68 g		

## Technical data

Description of article	Set of blades for Mini-Duro-Stripax up to AWG 24 for PTFE
------------------------	---

## Stripping tools

Cable type	Conductor with custom insulation	Colour	red
Max. conductor diameter	0.5 mm	Min. conductor diameter	0.3 mm
Stripping length, max.	7 mm	Stripping length, min.	3 mm

## Classifications

ETIM 6.0	EC001509	ETIM 7.0	EC001509
ETIM 8.0	EC001509	ECLASS 9.0	21-04-92-37
ECLASS 9.1	21-04-48-90	ECLASS 10.0	21-04-92-37
ECLASS 11.0	21-04-48-91	ECLASS 12.0	21-04-48-91

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

## Downloads

Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	