

# IN-LINE GLASS FUSEHOLDERS

150322



## Description

The 150322 is a 500 VAC/125 VDC rated inline fuseholder ideal for applications where supplemental protection is needed, such as lighting ballasts and power supplies. 8-inch pre-stripped wire leads and fuse clips come preassembled for quick installation.


## Features/Benefits

- Single piece body minimizes component count
- High voltage rating accommodates many power applications
- Wire leads are pre-attached to fuse clips for quick assembly
- Single piece molded body
- UL Recognized

## Recommended Fuses

3AG (312, 313 Series)  
3AB (314, 326, 505 Series)

## Dimensions in mm (inches)



## Specifications

<b>Voltage Rating:</b>	500 VAC, 125 VDC
<b>Ampere Rating:</b>	15 A
<b>Fuse Type:</b>	¼" x 1¼"
<b>Fuse Clips:</b>	Tin-plated brass
<b>Wire:</b>	Black 18 AWG, 150° C Stranded
<b>Molded Body:</b>	Single piece thermoplastic
<b>Flammability Rating:</b>	UL94 V-0
<b>Approvals:</b>	UL Recognized (File No. E14721)
<b>Environmental:</b>	RoHS compliant and Pb free
<b>Storage Temperature:</b>	-40° C to 80° C
<b>Operating Temperature:</b>	-55° C to 125° C

## Ordering Information

CATALOG NUMBER	SYSTEM NUMBER	STANDARD PACK
150322	01500322H	100 PIECES

## Web Resources

Sample requests, downloadable CAD drawings and other technical information: [www.littelfuse.com/150322](http://www.littelfuse.com/150322)

## Additional In-Line Glass Fuseholders

### Twist-Lock

155 Series  
RoHS Pb  
In-Line Mount  
Low Voltage 3AG, SFE



### Heavy-Duty Bayonet

155 Series  
RoHS Pb  
In-Line Mount  
Low Voltage 3AG




### Special Type

150 Series  
RoHS Pb  
In-Line Mount  
2AG, 5x20mm



## Dimensions in (inches)



## Web Resources

For more information, visit: [www.littelfuse.com/150](http://www.littelfuse.com/150)  
[www.littelfuse.com/155](http://www.littelfuse.com/155)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Littelfuse:](#)

[01500322H](#) [01500322.HXA](#) [01500332H](#) [150322](#)