



Plug 'n' Play compact axial fans


Complete with mountings and connector

- DC fans
- Plastic housing
- Ideal for PC cooling
- Molex connector fitted
- Threaded inserts for easy mounting
- Connection via lead 313mm (+/- 10mm)
- Threaded brass inserts fitted on both sides
- Blowing over struts
- Protection IP20

Part Number	Airflow	Airflow	Voltage	Voltage Range	Noise	Sound Power	Bearings	Power	Speed	Temp range	Length	Width	Depth	Insert thread size	Connector
	m ³ /h	CFM	VDC	VDC	dB(A)	Bel		W	RPM	°C	mm	mm	mm		
405F-RS0	8	4.7	5	4.5-5.5	22.1	4.4	Sleeve	0.7	5400	-20...+70	40	40	10	M3	Molex 22-01-2025
412FH-RS0	9	5.3	12	10-14	26	4.6	Sleeve	0.8	6000	-20...+70	40	40	10	M3	Molex 22-01-2025
412-RS0	10	5.9	12	10-14	18	3.8	Sleeve	0.9	6000	-20...+70	40	40	20	M3	Molex 22-01-2025
512F-RS0	20	11.8	12	10.8-13.2	30	4.5	Sleeve	1	5000	-20...+70	50	50	15	M3	Molex 22-01-2025
514F-RS0	20	11.8	24	21.6-26.4	30	4.5	Sleeve	1	5000	-20...+70	50	50	15	M3	Molex 22-01-2025
612F-RS0	29	17.1	12	10.8-13.2	27	4.4	Sleeve	1	3900	-20...+70	60	60	15	M3	Molex 22-01-2025
614F-RS0	29	17.1	24	21.6-26.4	27	4.4	Sleeve	1.1	3900	-20...+70	60	60	15	M3	Molex 22-01-2025
612NGN-RS0	41	24.1	12	18-15	35	5.2	Sleeve	2.1	5100	-20...+70	60	60	25	M3	Molex 22-01-2025
612NGHH-RS0	56	33	12	18-15	43	6.3	Sleeve	3.8	6850	-20...+70	60	60	25	M3	Molex 22-01-2025
614NGHH-RS0	56	33	24	18-28	43	6.3	Sleeve	3.8	6850	-20...+70	60	60	25	M3	Molex 22-01-2025

Fixing Centres

Frame Size	Dimension A (mm)
40	32
50	42
60	50



Terminal Assignment

- 1 = Red (+)
- 2 = Blue (-)

