

# Eco 2m Flexible LED Strip Light Kit



LED FLEXI STRIP

## Product Features

For an ambient light, this LED flexi strip light is suitable for domestic, commercial and retail internal lighting applications.

- Energy Saving
- Compact Strip with SMD LED technology
- IP20 Rated
- Driver included
- Available in Cool White, Warm White and Super Warm White
- 30K hours working life
- High Reliability & Efficiency
- 30 LEDs per metre
- Cuttable • 120° beam angle
- Suitable for indoor use



**ECO2MPC**  
Cool White



**ECO2MPW**  
Warm White



**ECO2MPS**  
Super Warm

Power  LED®

0845 533 0495

[www.powerled.uk.com](http://www.powerled.uk.com)

# LED FLEXI STRIP



## eco ECO2 2m Flexi Strip LED Light Kits

### What's included in the kit:

- 2 Metre ECO2 Flexi Strip Tape
- 1 x LED Power Driver - PCV1212



### ECO2 2m Flexi Strip LED Light Kits Specification

Part Code	ECO2MPC	ECO2MPW	ECO2MPS
Colour	Cool White	Warm White	Super Warm White
CCT (K)	5900-6100K	3900-4100K	2400-2600K
CCT (K) Nominal	6000K	4000K	2500K
LEDs per metre	30	30	30
Power per metre	2.4W	2.4W	2.4W
Available IP Ratings	IP20	IP20	IP20
Input Voltage	12VDC	12VDC	12VDC
Cuttable Length	100mm	100mm	100mm
Length	2m	2m	2m
Lumens	190lm	160lm	140lm
Angle	120°	120°	120°

### LED Driver - PCV1212

Part Code	PVC1212
Voltage	220V ~ 240VAC
Frequency	47 ~ 63 Hz
Power factor	0.80
Voltage	12V
Current	0-1.0A
Power	12W
R&N	400mV
Efficiency	80%
Over Load	Auto Recovery
Over Temperature	Thermal
Environment Temperature	-20 ~ +50°C, Storage: -20 ~ +70°C

Power  LED®

0845 533 0495

www.powerled.uk.com