



Click [here](#) for the 3D model.

Dimensions

L	5.3mm +/-0.2mm
W	5mm +/-0.2mm
T	3mm MAX
LL	1mm NOM
G	2.5mm +/-0.2mm

Packaging Specifications

Packaging	T&R, 330mm
Packaging Quantity	2500

General Information

Series	MPXV
Style	SMD
Chip Size	0530(2120)
Description	Surface Mount Inductor
Features	Power Inductors
RoHS	Yes
Qualifications	AEC-Q200
AEC-Q200	Yes
Core	Composite
Miscellaneous	40 (K) Temperature Rise Max.

Specifications

Inductance	0.68 uH
Inductance Tolerance	20%
Temperature Range	-55/+155°C
Shielded	Yes
Current	12.6 A (Irms, 40C Rise By Self Heating), 8 A (Isat, 20% Drop In Inductance), 12 A (Isat, 30% Drop In Inductance)
DC Resistance	8.2 mOhms
Self-Resonant Frequency	70 MHz