

# SEK CAB FLAT NSH RND AWG28/7 50P 30,48m



Part number	09 18 050 7008
Specification	SEK CAB FLAT NSH RND AWG28/7 50P 30,48m
HARTING eCatalogue	https://b2b.harting.com/09180507008

Image is for illustration purposes only. Please refer to product description.

#### Identification

Category	System cabling
Element	Bulk cables
Specification	Not assembled
Type of cable	Copper cable (round)

#### Version

Cable length	30.48 m
Number of cores	50
Core structure	AWG 28/7

#### Technical characteristics

Impedance	100 Ω
Limiting temperature	-30 +75 °C unmoved -20 +75 °C moved
Conductor resistance @ 20 °C	≤216 Ω/km

### Material properties

Material (cable)	PVC
Colour (cable)	Grey
RoHS	compliant
ELV status	compliant
China RoHS	е
REACH Annex XVII substances	No



# Material properties

REACH ANNEX XIV substances	No
REACH SVHC substances	No

## Specifications and approvals

Specifications	UL 1581 Sec. 1061 UL PLCC, CL2
CE	Yes

#### Commercial data

Packaging size	1
Net weight	4,660 g
Country of origin	USA
European customs tariff number	85444993
eCl@ss	27061801 Data and communication cable (copper)