



Click [here](#) for the 3D model.

| Dimensions | |
|------------|-----------------|
| L | 31mm +/-1mm |
| T | 22.5mm +/-1mm |
| H | 33mm +/-1mm |
| S | 19.5mm +/-0.5mm |
| S1 | 11mm +/-0.5mm |
| Wire Size | 0.8mm |

| Packaging Specifications | |
|--------------------------|--------|
| Packaging | Tray |
| Packaging Quantity | 200 |
| Component Weight | 26.1 g |

| General Information | |
|---------------------|--|
| Series | SS30V |
| Style | Through-Hole |
| RoHS | Yes |
| Notes | Replacement For SS35V Type And SS28V Type. |
| Miscellaneous | Temperature Rise Maximum: 50 K. |
| Core | Mn-Zn Ferrite |

| Specifications | |
|-------------------|------------|
| Voltage AC | 250 VAC |
| Inductance | 1.7 mH |
| Current | 4.5 A |
| Temperature Range | -25/+120°C |
| DC Resistance | 60 mOhms |