

Customer Information Sheet

DRAWING No.: M20-785XXXX

SHEET 3 OF 3


IF IN DOUBT - ASK

©

NOT TO SCALE

THIRD ANGLE PROJECTION

ALL DIMENSIONS IN mm




SPECIFICATION:

MATERIAL:
 MOULDING - HIGH TEMP. NYLON 6T UL94V-0
 CONTACT - PHOSPHOR BRONZE
FINISH:
 42 - GOLD ON CONTACT AREA,
 100% TIN ON TAILS, OVER NICKEL
 46 - 100% TIN ALL OVER, OVER NICKEL

ELECTRICAL:

CURRENT RATING - 3A
 VOLTAGE RATING - 500V AC
 CONTACT RESISTANCE - 20 MILLIOHMS MAX
 INSULATION RESISTANCE - 5,000 MEGOHMS MIN
ENVIRONMENTAL:
 TEMPERATURE RANGE - -40°C TO +105°C
 PACKING: TUBE
 FOR COMPLETE SPECIFICATION SEE COMPONENT SPEC C001XX (LATEST ISSUE).



NOTES:

1. ALL TOLERANCES ARE ±0.20 UNLESS OTHERWISE STATED.

ORDER CODE:

M20-785XXXX

No. OF WAYS PER ROW:

02 TO 40

FINISH:

42 = SELECTIVE GOLD + 100% TIN

46 = 100% TIN

RA	5	04.06.07	9767
NAME	ISS.	DATE	C/NOTE
APPROVED: <i>[Signature]</i>			
CHECKED: <i>[Signature]</i>			
DRAWN: J EVANS			
CUSTOMER REF.:			
ASSEMBLY DRG:			

HARWIN

THIS DRAWING AND ANY INFORMATION OR DESCRIPTIVE MATTER SET OUT HEREON ARE CONFIDENTIAL AND COPYRIGHT PROPERTY OF THE HARWIN GROUP AND MUST NOT BE DISCLOSED, LOANED, COPIED OR USED FOR MANUFACTURING, TENDERING OR FOR ANY OTHER PURPOSE WITHOUT THEIR WRITTEN PERMISSION.

TOLERANCES
 X = ±1mm
 X.X = ±0.25mm
 X.XX = ±0.10mm
 X.XXX = ±0.01mm
 ANGLES = ±5°
 UNLESS STATED

MATERIAL:
 SEE ABOVE

FINISH: SEE ABOVE

S/AREA: mm²

TITLE: 2.54mm PITCH DIL DUAL ENTRY PC TAIL SOCKET ASSEMBLY

DRAWING NUMBER:

M20-785XXXX

HARWIN USA
 TEL: 603 893 5376
 FAX: 603 893 5396
 mls@harwin.com

HARWIN Europe (UK)
 TEL: 023 9231 4545
 FAX: 023 9231 4590
 mls@harwin.co.uk

HARWIN Asia
 TEL: +65 6 779 4909
 FAX: +65 6 779 3868
 mls@harwin.com.sg

SHT
 3
 OF
 3