



## DCK266P2LR-GB – 18V XR Lanyard Ready Brushless Twin Kit – 2 x 5.0Ah Batteries



When working at heights on the jobsite it's important to adopt integrated solutions offering ultimate protection and secure the tool in case it drops. Lanyard ready integrated solutions offer options to tether select corded and cordless tools to rigid structures on jobsites when working at height with a maximum lanyard length of 2m, helping to secure the tool in case it is dropped\*. All Perform & Protect products are designed to consistently exceed health and safety regulations without compromising on performance.

The DCK266P2LR is a tether equipped, high quality power tool kit from DeWALT which includes and compact 2 speed combi drill and impact driver, a charger and 2 batteries. The Lanyard Ready equipped tools are suitable for working at height as well as day to day tasks on site. These power tool kits offer the ultimate drilling and driver experience for any project and the lithium-ion batteries also hold a longer charge than nickel batteries and can be charged more quickly.

### Features and Benefits:

- **DCD796 Combi Drill**
  - Two speed all metal transmission for increased runtime and longer tool life
  - Combi drill - Drill Driver and Hammer feature for multiple applications
  - 15 position adjustable torque control for consistent screw driving into a variety of materials
- **DCF887 Impact Driver**
  - 205Nm of torque ensures heavy applications are completed quickly
  - LED Halo ring work light – to illuminate your work area
  - 1/4 inch hex chuck
  - 3 speed for maximum control – includes PrecisionDrive
- Brushless Motor Technology for excellent efficiency, longer runtimes and increased performance
- Protection against overheating, overload and deep discharge conditions increases battery life
- Lanyard Ready tether is compatible with Lanyard Ready equipped 18V XR tools
- 2 stage carabiner for a secure hold, yet can be unhooked from the attachment point to charge the battery
- The integrated lanyard strap provides an attachment point for both battery and tool
- Visible safety – Any permanent stretch on the mounting point exposes a red colour indicator which shows the tether is now compromised and will need to be serviced before next use

**Specifications:**

- Power Source – Cordless
- Voltage – 18V
- Battery Capacity – 5.0Ah
- Battery Technology – Lithium Ion
  
- DCD796 Combi Drill
  - No Load Speed (Drilling/ Driving Mode) - 0-550/2000 rpm
  - Beats per Minute - 0-9350/34000 bpm
  - No Load Speed (Hammer Mode)
  - Power Output - 420 W
  - Max Torque (Soft) - 27 Nm
  - Max Torque (hard) – 70Nm
  - Chuck capacity - 1.5-13 mm
  - No. of Speeds - 2
  - Sound Pressure - 89 dB(A)
  - Sound Pressure Uncertainty - 3 dB(A)
  - Sound Power - 100 dB(A)
  - Sound Power Uncertainty - 3 dB(A)
  - Hand/Arm Vibration - Drilling into metal - <math><2.5\text{ m/s}^2</math>
  - Uncertainty K 1 (Vibration) - 1.5 m/s<sup>2</sup>
  - Hand/Arm Vibration - Hammer drilling into concrete - 11.5 m/s<sup>2</sup>
  - Uncertainty K 2 (Vibration) - 1.6 m/s<sup>2</sup>
  - Hand/Arm Vibration - Screw driving without impact - <math><2.5\text{ m/s}^2</math>
  - Uncertainty K 3 (Vibration) - 1.5 m/s<sup>2</sup>
  
- DCF887 Impact Driver
  - Max Torque – 205Nm
  - Speed Modes – 3
  - No Load Speed – 0- 1000/2800/3250
  - Impacts per Minute – 0-3800 IPM
  - Bit Holder – ¼" (6.35mm)
  - Power Output - 400 W
  - Sound Pressure - 96 dB(A)
  - Sound Power - 107 dB(A)
  - Sound Power Uncertainty - 3 dB(A)
  - Hand/Arm Vibration – Impact - 22 m/s<sup>2</sup>
  - Uncertainty K 1 (Vibration) - 2.1 m/s<sup>2</sup>

**Supplied with:**

- DCD796 18v Li-Ion XR Brushless Combi Drill Complete with Lanyard Ready Tether Mount
- DCF887 18V Brushless G2 3 Speed Impact Driver Complete with Lanyard Ready Tether Mount
- 2 x DCB184LR 18V 5.0Ah Battery with Lanyard Ready Tether Mount
- Multi-voltage XR charger
- DeWALT Soft Bag