

领亚电子科技股份有限公司

No.2, The
Fourth West Industrial Road, High-Tech Industrial Development Zone,
Songshan Lake, Dongguan City, Guangdong Province, China
Tel:(86)-769-85550688 Fax:(86)-769-85550388

承 认 书

SPECIFICATION FOR APPROVAL

产 品: F/UTP CAT. 5e 24AWG×4P SOLID

PRODUCT

料 号: _____

承认书编号: TX-024A0801-A

PART NO.

SHEET NO.

客户名称: YAKOVLEFF

客户 料号: L-FTP4-S Cat5e

CUSTOMER

CUSTOMER NO.

UL/CSA STANDARD: _____

Non-standard: _____

日 期: 2020-2-11

DATE:

CUSTOMER CONCLUSION: APPROVED (承认)
(客户判定)

LIMIED (允收)

REJECT (拒收)

CONDITIONAL APPROVAL (条件认可)

INCLUDING THIS COVER TOTAL 3 PAGES
(含封面页共 3 页)

* PLEASE SIGNED AND FAX THE RESULT TO US.
(请于判定签名后将结果传回)

AUTHORIZED SIGNATURES

领亚电子科技股份有限公司

No.2, The Fourth West Industrial Road, High-Tech Industrial Development Zone,
Songshan Lake, Dongguan City, Guangdong Province, China

Tel:(86)-769-85550688

Fax:(86)-769-85550388

CABLE SPECIFICATION(线材承认书)

SPEC NO.	TX-024A0801		PART NO.	
UL FILE NO.		UL STYLE		NON-STANDARD
CSA FILE NO.		CSA STYLE		版本 A
CONSTRUCTION ITEM/ 结构项目		结构项目		
CONDUCTOR 导体	CONSTRUCTION 构造规格	AWG	1/0.510±0.005	
	MATERIAL/导体材质	-----	BARE SOLID COPPER CONDUCTOR	
INSULATION 绝缘	MATERIAL/材质	-----	HDPE	
	OD / 芯线外径	mm	1.03±0.05	
	AVERAGE THICKNESS 平均厚度	mm	0.25(REF)	
	COLOR / 颜色	-----	1P. BROWN & WHITE / BROWN 2P. BLUE & WHITE / BLUE 3P. ORANGE & WHITE / ORANGE 4P. GREEN & WHITE / GREEN	
INNER-ASSEMBLE 内集合	OD/绞合外径	mm	/	
FILLER 填充	MATERIAL/材质	-----	/	
	CONSTRUCTION/构造	%	/	
INSIDE-TAPE WRAP 内部包装	MATERIAL/包带材质	-----	MYLAR	
	CONDUCTIVE/导电面	-----	/	
	OVERLAP RATE/重叠率	%	25%	
DRAIN WIRE 地 线	CONSTRUCTIO/构造	mm	1/0.404±0.007	
	MATERIAL/导体材质	-----	COPPER COVER STEEL	
OUTSIDE-TAPE WRAP 外部包装	MATERIAL/包带材质	-----	AL-MYLAR	
	CONDUCTIVE/导电面	-----	OUTSIDE	
	OVERLAP RATE/重叠率	%	25%	
WEAVING 编织	CONSTRUCTION 构造规格	mm	/	
	MATERIAL/导体材质	-----	/	
JACKET 外被 INNER-ASSEMBLE 内集合	OD/绞合外径	mm	/	
	MATERIAL/材质	-----	PVC	
	DIAMETER/线径	mm	5.9±0.35	
	AVERAGE THICKNESS 平均厚度	mm	0.55(REF)	
	COLOR/颜色	-----	GREY PANTONE cool gray 5C	
MARKING 喷字	MARKING COLOR/ 喷字颜色	-----	BLACK	
	JACKET 外被	-----	LAN CABLE FTP CAT.5E 24AWG 4PAIRS SOLID ***M (001M-305M)	

<p>领亚电子科技股份有限公司 No.2, The Fourth West Industrial Road, High-Tech Industrial Development Zone, Songshan Lake, Dongguan City, Guangdong Province, China Tel:(86)-769-85550688 Fax:(86)-769-85550388 CABLE SPECIFICATION(线材承认书)</p>					
SPEC NO.	TX-024A0801		PART NO.		
UL FILE NO.		UL STYLE		NON-STANDARD	
CSA FILE NO.		CSA STYLE		版本	A
<p>Electric characters</p> <p>1.Voltage rating(额定电压) 30V</p> <p>2.Temperature rating(额定温度) 75°C</p> <p>3.Dielectric strength(耐压强度) AC-500V/MIN</p> <p>4.Insulation resistance(绝缘电阻) 100 M OHMS.KM MIN at 20°C</p>					
<p>Physical Characters</p> <p>1.Tensile strength before aging(老化前抗张强度测试)</p> <p> 1.1 Jacket : $\geq 1.05\text{kg/mm}^2$</p> <p>2.Elongating before aging (老化前断裂伸长率)</p> <p> 2.1 Jacket : $> 100\%$</p>					
<p>Environmental requirements: 1. 不含双方签订的环保标准的 1 级管理物质</p>					
<p>Cross drawing: 截面示意图</p> <div style="text-align: center;"> </div>					
APPROVER		CHECK		DESIGNER	LLL