

领亚电子科技股份有限公司

No.2, The
Fourth West Industrial Road, High-Tech Industrial Development Zone,
Songshan Lake, Dongguan City, Guangdong Province, China
Tel:(86)-769-85550688 Fax:(86)-769-85550388

承 认 书

SPECIFICATION FOR APPROVAL

产 品: FTP CAT. 6 23AWG×4P SOLID PVC

PRODUCT

料 号: _____

PART NO.

客户名称: YAKOVLEFF

CUSTOMER

承认书编号: TX-023A0646-A

SHEET NO.

客户 料号: L-FTP4-S Cat6

CUSTOMER NO.

UL/CSA STANDARD: _____

Non-standard: _____

日 期: 2020-2-11

DATE:

CUSTOMER CONCLUSION: ☐ APPROVED (承认)
(客户判定)

☐ LIMIED (允收)

☐ REJECT (拒收)

☐ CONDITIONAL APPROVAL (条件认可)

INCLUDING THIS COVER TOTAL 3 PAGES
(含封面页共 3 页)

* PLEASE SIGNED AND FAX THE RESULT TO US.
(请于判定签名后将结果传回)

AUTHORIZED SIGNATURES

领亚电子科技有限公司


No.2, The Fourth West Industrial Road, High-Tech Industrial Development Zone,
Songshan Lake, Dongguan City, Guangdong Province, China

Tel:(86)-769-85550688

Fax:(86)-769-85550388

CABLE SPECIFICATION(线材承认书)

SPEC NO.	TX-023A0646		PART NO.		
UL FILE NO.		UL STYLE		NON-STANDARD	
CSA FILE NO.		CSA STYLE		版本	A
CONSTRUCTION ITEM/ 结构项目		结构项目			
CONDUCTOR 导体	CONSTRUCTION 构造规格	AWG	1/0.570±0.005		
	MATERIAL/导体材质	-----	BARE SOLID COPPER CONDUCTOR		
INSULATION 绝缘	MATERIAL/材质	-----	HDPE		
	OD / 芯线外径	mm	1.15±0.10		
	AVERAGE THICKNESS 平均厚度	mm	0.29 (REF)		
	COLOR / 颜色	-----	1P. BROWN & WHITE / BROWN 2P. BLUE & WHITE / BLUE 3P. ORANGE & WHITE / ORANGE 4P. GREEN & WHITE / GREEN		
INNET-ASSEMBLE 内集合	OD/绞合外径	mm	5.6(REF)+CORSS		
INSIDE-TAPE WRAP 内部包装	MATERIAL/包带材质	-----	MYLAR		
	CONDUCTIVE/导电面	-----	/		
	OVERLAP RATE/重叠率	%	25%		
DRAIN WIRE 地 线	CONSTRUCTIO/构造	mm	1/0.404±0.007		
	MATERIAL/导体材质	-----	COPPER COVER STEEL		
OUTSIDE-TAPE WRAP 外部包装	MATERIAL/包带材质	-----	AL-MYLAR		
	CONDUCTIVE/导电面	-----	INSIDE		
	OVERLAP RATE/重叠率	%	25%		
JACKET 外被 INNET-ASSEMBLE 内集合	MATERIAL/材质	-----	PVC		
	DIAMETER/线径	mm	7.3±0.35		
MARKING 喷字	AVERAGE THICKNESS 平均厚度	mm	0.65±0.05		
	COLOR/颜色	-----	GREY PANTONE cool gray 5C		
	MARKING COLOR/ 喷字颜色	-----	BLACK		
	JACKET 外被	-----	LAN CABLE FTP CAT.6 23AWG 4PAIRS SOLID ***M (001M-305M)		

领亚电子科技有限公司 No.2, The Fourth West Industrial Road, High-Tech Industrial Development Zone, Songshan Lake, Dongguan City, Guangdong Province, China Tel:(86)-769-85550688 Fax:(86)-769-85550388 CABLE SPECIFICATION(线材承认书)					
SPEC NO.	TX-023A0646		PART NO.		
UL FILE NO.		UL STYLE		NON-STANDARD	
CSA FILE NO.		CSA STYLE		版本	A
Electric characters 1.Voltage rating(额定电压) 30V 2.Temperature rating(额定温度) 75℃ 3.Dielectric strength(耐压强度) AC-500V/MIN 4.Insulation resistance(绝缘电阻) 100 M OHMS.KM MIN at 20℃					
Physical Characters 1.Tensile strength before aging(老化前抗张强度测试) 1.1 Jacket : >1.05kg/mm² kg/mm² 2.Elongating before aging (老化前断裂伸长率) 2.1 Jacket : > 100%					
Environmental requirements: 1. 不含双方签订的环保标准的 1 级管理物质					
Cross drawing: 截面示意图 					
APPROVER		CHECK		DESIGNER	LLL