

Specifications	Range	Resolution
MS2108		
DC Voltage	660mV/6.6V/66V/600V	0.1mV/0.001V/0.01V/0.1V
AC Voltage	660mV/6.6V/66V/600V	0.1mV/0.001V/0.01V/0.1V
AC Current	66A/600A	0.01A/0.1A
Resistance	660Ω/6.6kΩ/66kΩ 660kΩ/6.6MΩ/66MΩ	0.1Ω/0.001kΩ/0.01kΩ/ 0.1kΩ/0.001kΩ/0.01MΩ