

Transmitter	Wiremap	Cable type	CAT5、CAT6 (STP & UTP)
		Test with switch directly	Yes
		Max range	600m
	Length	Cable type	CAT5、CAT6 (STP & UTP)
		Test range	2~200m
		Accuracy	±1.6m
		Breakage location	Yes
	Scan	Cable type	CAT5、CAT6 (STP & UTP)
		Max. signal voltage	8Vp-p
		Frequency	130KHz
		AC filter	Yes
	POE	Max range	600m
		Test range	DC 5~60V standard / non-standard PoE switch
		Voltage display	Yes
		PoE type	IEEE 802.3af/at
	LCD display	128*64 Dot-matrix with backlight	
	Power supply	AAA*3 (Not included)	
	Low battery warning	2.7V	
	Auto-off time	15min、30min、60min、OFF	
	Voltage protection	DC48V 5mA	
	Max working current	<150mA	
Receiver	Sensitivity adjustable	Yes	
	AC Voltage detecting	Yes	
	Lamp	Yes	
	Battery type	9V*1 (Not included)	
	Low battery warning	6± 0.5V	
	Max working current	<100mA	
Remote	Wiremap Port	RJ45	
	Voltage protection	DC48V 5mA	