

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)



Touch panel with 10,92 cm / 4,3"-TFT-display (analog resistive (polyester)), 480 x 272 Pixel(s) (WQVGA), 262144 colors, ARM9 $^{\text{TM}}$ i.MX28, 454 MHz, 2x COM (RS-232/422/485), 1x USB 2.0, Typ A, 1x USB 2.0, Typ B, 1 x Ethernet (10/100 Mbps), RJ45, Windows CE 6.0 and user software: Visu+. (bus system: without)

Similar figure

Your advantages

- ✓ Visu+ RT integrated as standard in all BTP 2000 devices
- ☑ Connection to all relevant control systems, thanks to a large number of available drivers
- ☑ Developed for basic applications with attractive price/performance ratio
- 3 display sizes in 16:9 format



Key Commercial Data

Packing unit	1 pc
GTIN	4 055626 666587
GTIN	4055626666587
Weight per Piece (excluding packing)	200.000 g
Custom tariff number	84714100
Country of origin	India

Technical data

Note

Utilization restriction	area
Dimensions	
External dimension, width	120 mm
External dimension, height	89 mm
External dimension, depth	5 mm
Note regarding external dimension	Dimensions of the front plate
Installation dimension, width	111 mm
Installation dimension, height	80 mm

EMC: class A product, see manufacturer's declaration in the download



Technical data

Dimensions

Installation dimension, depth	31.5 mm
Note regarding installation dimension	Installation cutout

Display

Display	10,92 cm / 4,3"-TFT
Screen resolution	480 x 272 Pixel(s) (WQVGA)
Backlighting	LED
Display backlight MTBF	20000 h
Touch technology	analog resistive (polyester)
Colors	262144 colors

Computer data

Processor	ARM9 [™] i.MX28, 454 MHz
Operating system	Windows® CE 6.0
User software	Visu+
RAM	128 MB DDR2 SDRAM
Mass storage	Flash, 512 MB
Network	1 x Ethernet (10/100 Mbps), RJ45
Interfaces	2x COM (RS-232/422/485)
	1x USB 2.0, Typ A
	1x USB 2.0, Typ B
Bus system	without
Slots	1x SD

General

Material front plate	Plastic
Housing material	Plastic
Mounting type	Front installation
Weight	200 g

Ambient conditions

Degree of protection	IP66 (on the front), IP20 (on the back)
Ambient temperature (operation)	0 °C 50 °C
Ambient temperature (storage/transport)	-20 °C 85 °C
Permissible humidity (operation)	10 % 95 % (non-condensing)
Permissible humidity (storage/transport)	10 % 95 % (non-condensing)
Vibration (operation)	DIN EN 60068-2-6
Shock	DIN EN 60068-2-27

Device supply

Typical current consumption	0.17 A
Power supply unit	24 V DC ±15 %

Standards and Regulations



Technical data

Standards and Regulations

Shock	DIN EN 60068-2-27
Vibration (operation)	DIN EN 60068-2-6

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Classifications

eCl@ss

eCl@ss 5.1	27330200
eCl@ss 6.0	27242300
eCl@ss 7.0	27242302
eCl@ss 8.0	27242302
eCl@ss 9.0	27330201

ETIM

ETIM 4.0	EC001412
ETIM 5.0	EC001412
ETIM 6.0	EC001412

Accessories

Accessories

Data plug

D-SUB gender changer - VS-09-GC-ST/ST - 1652651



D-SUB contact insert, shell size 1, with nine signal contacts, type of contact pin, gender changer, fixing with 4-40 UNC thread

Operating stylus

Touch pen - TOUCH PEN - 2701379



Touch pen for HMIs, silver coated. Delivery includes self-adhesive pen holder.



Accessories

PCB plug

Printed-circuit board connector - MSTB 2,5/ 3-STF-5,08 - 1777992

PCB connector, nominal current: 12 A, rated voltage (III/2): 320 V, number of positions: 3, pitch: 5.08 mm, connection method: Screw connection with tension sleeve, color: green, contact surface: Tin



Storage medium

USB memory stick - USB FLASH DRIVE - 2402809



USB memory stick, 8 GB

Phoenix Contact 2018 © - all rights reserved http://www.phoenixcontact.com