

## Coaxial Cable Connector 16\_4310-50-5-Z1/003\_-

### Description

Right angle cable plug

Interface standards

IEC 61169-54



### Technical Data

#### Electrical Data

Impedance	50 Ω
Interface frequency max.	12 GHz

#### Mechanical Data

Centre contact	soldered
Outer contact	soldered
Weight	0.0343 kg

#### Environmental Data

Operating temperature 2011/65/EU, RoHS	-55 °C to 90 °C compliant
---	------------------------------

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Silver Plating
Outer contact	Brass	Silver Plating
Body	Brass	Silver Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	NBR (Nitrile butadiene rubber)	

### Related Documents

Outline drawing	DOU-00261757
Catalogue drawing	DCA-00264977
Assembly instruction	DOC-0000453743

### Ordering Information

Bulk 100 pcs package	16_4310-50-5-Z1/003_-H
Single package	16_4310-50-5-Z1/003_-E

### Additional Information

Suitable cables	SUCOFORM_250-01_FEP, EZ_250_M17
-----------------	---------------------------------