

Coaxial Cable Connector 11_UHF-0-7-17/033_-

Description

Straight cable plug

Interface standards
IEC 60169-12



Technical Data

Electrical Data

Impedance other Ω
Interface frequency max. 0.2 GHz

Mechanical Data

Centre contact crimped
Outer contact crimped
Weight 0.0238 kg

Environmental Data

Operating temperature -55 °C to 165 °C
2011/65/EU (RoHS - including
2015/863 and 2017/2102) compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Silver Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PSU (Polysulfone)	
Coupling nut	Brass	SUCOPLATE (R) Plating
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Related Documents

Outline drawing DOU-00181576
Catalogue drawing DCA-00045040
Assembly instruction DOC-0000201061

Ordering Information

Single package 11_UHF-0-7-17/033_-E

Additional Information

Suitable cables RG_213_/U, GX_07272, G_07262, G_07272, RADOX_RF_213

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[11_UHF-0-7-17/033_-E](#)