

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2147572023

Status:


Active

Overview:

Micro-Fit Connector System

Description:

Micro-Fit 3.0 Male-to-Micro-Fit 3.0 Male Off-the-Shelf (OTS) Cable Assembly, Dual Row, 600.00mm Length, Gold (Au) Plating, 2 Circuits, Black



Series image - Reference only

Documents:

[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

[Datasheet \(PDF\)](#)

General	
Product Family	Cable Assemblies
Series	214757
Application	Power, Wire-to-Wire
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Micro-Fit 3.0 Both Ends
Overview	Micro-Fit Connector System
Product Name	Micro-Fit 3.0
Type	Discrete Wire Assembly
UPC	193264501809
Physical	
Cable Length	600.00mm
Circuits (Loaded)	2
Color - Resin	Black
Gender	Male-Male
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	13.500/g
Number of Rows	2
Packaging Type	Bag
Pitch - Mating Interface	3.00mm
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.85mm max.
Wire Size AWG	18
Wire/Cable Type	UL 1061
Electrical	
Current - Maximum per Contact	8.5A
Material Info	
Reference - Drawing Numbers	
Sales Drawing	2147572020-000

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - ECHA_01_2020 (16 January 2020	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

214757 Series

Mates With

Micro-Fit 3.0 Receptacle Housings [43025](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION