


Mod. 7626.B

COPOLYMER POLYPROPYLENE WATERPROOF CASE

Large cases IP67 certified. Two man lift side handles and retractable handle. Self-oiling free running wheels. Four colors available and two internal standard configurations.




METRIC MM-KG-C°



INTERNAL DIMENSIONS		EXTERNAL DIMENSIONS		OTHER DATA	
L LENGTH	763 mm	L LENGTH	832 mm	WEIGHT EMPTY	7.7 Kg
W WIDTH	399 mm	W WIDTH	466 mm	WEIGHT WITH FOAM	9.5 Kg
D DEPTH	260 mm	D DEPTH	279 mm	WEIGHT WITH CUSTOM FOAM	Kg
LID	50 mm			VOLUME	79.2 lt
BASE	210 mm			BUOYANCY	57.5 Kg/max
				OPERATING TEMPERATURE	°C min -33 / max 90

IMPERIAL IN-LBS-F°



INTERNAL DIMENSIONS		EXTERNAL DIMENSIONS		OTHER DATA	
L LENGTH	30 1/16 in	L LENGTH	32 3/4 in	WEIGHT EMPTY	16.97 lbs
W WIDTH	15 11/16 in	W WIDTH	18 3/8 in	WEIGHT WITH FOAM	20.94 lbs
D DEPTH	10 1/4 in	D DEPTH	11 in	WEIGHT WITH CUSTOM FOAM	lbs
LID	1 15/16 in			VOLUME	20.92 gal
BASE	8 1/4 in			BUOYANCY	126.77 lbs/max
				OPERATING TEMPERATURE	°F min -27.4 / max 194