


JKL LAMP PART NUMBER	COLOR	STARTING CIRCUIT VOLTAGE VS (Vrms)	OPERATING LAMP VOLTAGE VL (Vrms)	OPERATING LAMP CURRENT IL (mA rms)	BRIGHTNESS (CANDELA/m <sup>2</sup> )	*RATED LIFE (HRS)
BF26240-24B	LCD HIGH OUTPUT WHITE 11000°k RGB	1250 @ 0°C	505	5	30,000 ± 10%	20,000

\* RATED LIFE IS DEFINED AS THE POINT AT WHICH THE INTENSITY BECOMES 50% OF THE INITIAL RATING.

			<b>METRIC</b>  THIRD ANGLE PROJECTION		DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0 2 PL +/- 0 ANGLE +/- 0		<b>JKL COMPONENTS CORPORATION</b>				
					TITLE <b>MINIATURE COLD CATHODE FLUORESCENT LAMP</b>						
DRAWN BY <b>L. WENGSTROM</b>			APPVD BY DATE <b>FD 10/17/00</b>		SIZE <b>A</b>	FSCM NO. <b>55335</b>	DRAWING NO. <b>BF26240-24B</b>				
REV. NO. A DIM LINE CORRECT. AND 240+/-5.0 TO 240+/-3.0 RELEASED			10/17/00 5/22/00		SCALE <b>NONE</b>		RELEASED DATE <b>5/22/00</b>	REVISION DATE <b>10/17/00</b>	REV. NO. A	SHEET 1 OF 1	
DESCRIPTION/ECO NUMBER			APPVD DATE		- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED						

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JKL Components:](#)

[BF26240-24B](#)