


JKL PART NUMBER	LENGTH A +/- 1.5mm	COLOR (REF.)	STARTING CIRCUIT VOLTAGE VS (Vrms)	OPERATING LAMP VOLTAGE VL (Vrms)	OPERATING LAMP CURRENT IL (mAmps)	BRIGHTNESS (Cd/m ²)	*RATED LIFE (HRS)
BF20218-24B	218mm	RGB HIGH OUTPUT WHITE 8400°k x = .290 y = .305	1250 @ 0°C	500	5 ± 1	46,000 TYP.	20,000 MIN. 40,000 AVG.
BF20226-24B	226mm		1275 @ 0°C	510			
BF20292-24B	292mm		1650 @ 0°C	660			
BF20325-24B	325mm		1830 @ 0°C	735			

*NOTE: RATED LIFE IS DEFINED AS THE POINT AT WHICH THE INTENSITY BECOMES 50% OF THE INITIAL RATING.

			METRIC  THIRD ANGLE PROJECTION		DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0.2 2 PL +/- 0 ANGLE +/- 0		JKL COMPONENTS CORPORATION				
					TITLE MINIATURE COLD CATHODE FLUORESCENT LAMP						
A RATING ADDITIONS & CHANGES RELEASED TO CAD MULTI LIST			DRAWN BY L. WENGSTROM		APPV'D BY DATE J.K. 4/26/04		SIZE A	FSCM NO. 55335	DRAWING NO. BF 20-24B		
REV. NO. DESCRIPTION/ECO NUMBER APPV'D DATE			- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED		SCALE NONE		RELEASED DATE 8/14/03	REVISION DATE 4/26/04	REV. NO. A	SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JKL Components:](#)

[BF20226-24B](#)