



**RoHS  
Compliant  
Drawing For  
Reference Only**



**Technical requirement :**

1. This product should meet EU RoHS related requirement.
2. The surface of plastic part should be without any crackle such as burr,lack,and so on phenomenon.
3. The surface of metal part should be without any defect such as scour,nick,oxidation and plating problem.
4. The electronic performance should be the same as spec.

**Specification :**

Insertion & Extraction Force : 0.5 Kg. Min.  
 Dielectric Strength For 60 Seconds : AC 1000V Min.  
 Suitable Rated Current : 5A 250V  
 Insulation Resistance At 500V DC : 100M  $\Omega$  Min  
 Temperature Rise : 50°C Max.  
 Voltage Drop : 20mV Max.

**DCI DRAGON CITY INDUSTRIES LIMITED**

			Design	K.W Law	Remark		Scale	
			Drawing	W.K Yeung	Remark		Material	
Item Name	FUSE HOLDER FOR 5 X 20 MM FUSE	Tolerance :	Check	K.L Wong	Remark		Drawing No.	B009111623
Item No.	FH-101-HZ	Unit : mm	Approval	K.W Chan	Remark		Sheet	