
| 27.7 |
|------|
| |
| |


| | | REVISIONS | | | |
|-----|-----|------------------------|-----------|-----|------|
| REV | ECO | DESCRIPTION | DATE | BY | APPR |
| А3 | - | RELEASE NEW DWG FORMAT | 18/JUN/13 | DRP | - |


PLUG, 2 SOCKET, ATM SERIES

ATM06-2S-XXX

⁵ A3








NOTES: UNLESS OTHERWISE SPECIFIED

MATERIAL:

HOUSING: THERMOPLASTIC SEAL: SILICONE RUBBER

- 2. MODIFICATIONS: N/A
- 3. SPECIFICATIONS:
 - 3.1 CURRENT RATING: 7.5 AMPS
 - 3.2 OPERATING TEMPERATURE: -55°C TO +125°C
 - 3.3 DIELECTRIC WITHSTANDING VOLTAGE: LESS THAN 2 MILLIAMPS CURRENT LEAKAGE @ 1500 VOLTS AC.
 - 3.4 INSULATION RESISTANCE: 1000 MEGOHMS MIN @ 25°C.
 - 3.5 MOISTURE RESISTANCE: IP67 (MATED CONDITION)
 - 3.6 MATING CYCLE DURABILITY: 100 CYCLES
 - 3.7 RoHS COMPLIANT
- 4. MATING PART: ATM04-2P* RECEPTACLE. (* = MODIFICATIONS AND/OR COLORS)
- 5. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.
- 6 CONTACT SIZE AND REAR SEAL WIRE RANGE:

| CONTACT | MIN. INSUL | MAX. INSUL | TYPICAL |
|---------|----------------------|----------------------|-------------|
| SIZE | O.D. | O.D. | WIRE RANGE |
| 20 | 1.35 mm (.053 in) | 3.05 mm (.120 in) | 16 - 22 AWG |



| PART NUMBER CHART | | | |
|---------------------|--------------|--|--|
| COLOR PART NUMBER | | | |
| GREY ATM06-2S | | | |
| BLACK | ATM06-2S-BLK | | |
| BLUE ATM06-2S-BLU | | | |
| BROWN ATM06-2S-BRN | | | |
| GREEN ATM06-2S-GRN | | | |
| RED ATM06-2S-RED | | | |
| WHITE | ATM06-2S-WHT | | |
| YELLOW ATM06-2S-YEL | | | |

STANDARD MOLDED COLOR IS GREY. ADDITIONAL COLORS SHOWN IN PART NUMBER CHART ARE AVAILABLE VIA SPECIAL ORDER.

| SEE PART N | UMBER CHART | | | |
|--|--|--|--|--------|
| PART N | PART NUMBER | | DESCRIPTION | ITEM |
| QUANTITY | MA | TERI | ALS LIST | |
| UNLESS OTHERWISE SPECIFIED 1) All dimensions are in metric(mm). | SIGNATURE | S DATE | Amphor | |
| 2) Tolerances are as follows: 1 PL DEC ±0.30 Fractions +1/64 | D.PARKS | 18/JUN/13 | Ampher | 101 |
| 2 PL DEC ±0.15 3 PL DEC ±0.08 | CHECKED: | | Sine Systems - www.amphenol-sin | ie.com |
| 3) Note reference = X | ENGINEER: | | 44724 Morley Drive Clinton Township, MI 48036 | |
| MATERIAL SPECIFICATIONS: | APPROVAL: | | | |
| | CUSTOMER: | | PLUG, 2 SOCKET, ATM SE | ERIES |
| PROCESS SPECIFICATIONS: | THIS DRAWING IS SUPPLI INFORMATION ONLY. DES | IGN FEATURES, | | |
| PROCESS SPECIFICATIONS. | SPECIFICATIONS AND PEI SHOWN HEREON ARE THI THE AMPHENOL CORPOR OF REPRODUCTION ARE DIMENSIONS ARE SUBJECT | E PROPERTY OF LATION. NO RIGHTS IMPLIED. ALL | B C- ATM06-2S-XX | XX A3 |
| NEXT ASS'Y: | MANUFACTURING VARIAT | TIONS. | SCALE: NONE SHEET | 1 of 1 |

A Series™ - Contact Size 20 Options (Works with: ATM, DuraMate and PanelMate Series)

| Machined Contacts, Sockets & Pins | | | | |
|-----------------------------------|--|------|-------|----------|
| Part Number | Description | Size | AWG | Туре |
| AT60-010-2031 | Male Contact - Pin, Gold-plated | 20 | 16-18 | Machined |
| AT62-005-20141 | Female Contact - Socket, Gold-plated | 20 | 16-18 | Machined |
| AT60-010-20141 | Male Contact - Pin, Nickel-plated | 20 | 16-18 | Machined |
| AT62-005-2031 | Female Contact - Socket, Nickel-plated | 20 | 16-18 | Machined |
| AT60-202-2031 | Male Contact - Pin, Gold-plated | 20 | 20-22 | Machined |
| AT62-201-2031 | Female Contact - Socket, Gold-plated | 20 | 20-22 | Machined |
| AT60-202-20141 | Male Contact - Pin, Nickel-plated | 20 | 20-22 | Machined |
| AT62-201-20141 | Female Contact - Socket, Nickel-plated | 20 | 20-22 | Machined |

| Tooling - Machined Contacts | | |
|-----------------------------|---|--|
| Part Number | Description | |
| AUTK-20 | Hand Crimp Tool, Size 20 | |
| AUTK-100 | Universal Heavy Duty Contact Crimping Tool Kit, Size 12/16/20 | |
| CA-5D12 | Universal Hand Crimp Tool, Size 12/16/20 | |
| CA-5E12 | Pneumatic Crimp Tool, Size 12/16/20 | |

| | Stamped & Formed Contacts, Sockets & Pins | | | | |
|--------------|---|------|-------|------------------|--|
| Part Number | Description | Size | AWG | Туре | |
| AT60-20-0144 | Male Contact - Pin, Gold-plated | 20 | 16-22 | Stamped & Formed | |
| AT62-20-0144 | Female Contact - Socket, Gold-plated | 20 | 16-22 | Stamped & Formed | |
| AT60-20-0244 | Male Contact - Socket, Gold-plated | 20 | 16-22 | Stamped & Formed | |
| AT62-20-0244 | Female Contact - Socket, Gold-plated | 20 | 16-22 | Stamped & Formed | |
| AT60-20-0122 | Male Contact - Pin, Nickel-plated | 20 | 16-22 | Stamped & Formed | |
| AT62-20-0122 | Female Contact - Socket, Nickel-plated | 20 | 16-22 | Stamped & Formed | |
| AT60-20-0222 | Male Contact - Socket, Nickel-plated | 20 | 16-22 | Stamped & Formed | |
| AT62-20-0222 | Female Contact - Socket, Nickel-plated | 20 | 16-22 | Stamped & Formed | |
| AT60-20-0277 | Male Contact - Socket, Tin-plated | 20 | 16-22 | Stamped & Formed | |
| AT62-20-0277 | Female Contact - Socket, Tin-plated | 20 | 16-22 | Stamped & Formed | |
| AT60-20-0422 | Male Contact - Socket, Nickel-plated | 20 | 20-22 | Stamped & Formed | |
| AT62-20-0444 | Female Contact - Socket, Gold-plated | 20 | 20-22 | Stamped & Formed | |

| Tooling - Stamped & Formed Contacts | | |
|-------------------------------------|---|--|
| MFX-3974 | Crimp Die - Size 20 | |
| MFX-3976 | Crimp Die - Size 20 (20-22AWG -04XX Series) | |
| MFX-3978 | Crimp Die - Size 20 (20-22AWG -02XX Series) | |
| ATT-20-00 | Hand Crimp Tool - Size 20 (20AWG) | |

| Contact Removal Tools (For both Machined or Stamped & Formed Contacts) | | |
|--|--|--|
| Part Number Description | | |
| ATRT-100 | Contact and Wedgelock Extraction Tool | |
| AT11-240-2005 | Contact Removal Tool, Plastic, Size 20 | |

| Sealing Plugs (For both Machined or Stamped & Formed Contacts) | | |
|--|--|--|
| Part Number | Description | |
| AT13-204-2005 | Sealing Plug, Size 20, White | |
| AT13-204-2005-SR | Sealing Plug, Size 20, SR01 Series, Black | |
| ATM13-217-2005 | Locking Sealing Plug, Size 20, Grey | |
| ATM13-217-2005-SR | Locking Sealing Plug, Size 20, SR01 Series, Blue | |