

## Datasheet

### Line Mounting Hydraulic Flow Control Valve 201012, BSP 3/8, 210 bar

RS Stock number [283-3997](#)



They allow for regulations of flow in both directions. Suitable for applications with air, gas and liquid in general. As an alternative to FT 257/2 where the working pressure does not exceed 210 bar and when ferrous materials cannot be used. Same basic characteristics as the FT 257 series:  
accurate flow regulations efficient metallic sealing  
simple setting of flow rates secure against accidental needle withdrawal secure needle position with locking screw inserted in the handwheel provisions for panel mounting.  
For use with pressure up to 210 bar

**Materials:**

**Body** OT 58 - UNI 5705 - Nickel plated

**Needle** X 10 Cr Ni S 1809 - UNI 6900 aluminium

**OR** Nitrile

**Antiextrusion ring** PTFE

**Handwheel ma** GD- Al Si 12 - UNI 5706 aluminium

**Handwheel mp** ABS plastic