


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



| PANDUIT PART NO. | BUNDLE DIA. | | A in (mm) | B in (mm) | C in (mm) | D in (mm) | E in (mm) | F in (mm) | MIN. LOOP TENSILE lbs. (N) | CROSS SECTION | WEIGHT lbs./100 pcs. (g) |
|------------------|--------------|--------------|--------------|--------------|--------------|--------------|--------------|--------------|-------------------------------|---------------|--------------------------------|
| | MIN. in (mm) | MAX. in (mm) | | | | | | | | | |
| BT2LH | .188 (4.8) | 2.00 (51) | .065 (1.7) | .275 (7.0) | .325 (8.3) | .320 (8.1) | .520 (13.2) | 8.7 (221) | 120 (534) | LIGHT HEAVY | .59 (267) |
| BT3LH | .188 (4.8) | 3.00 (76) | .065 (1.7) | .275 (7.0) | .325 (8.3) | .320 (8.1) | .520 (13.2) | 11.8 (300) | 120 (534) | LIGHT HEAVY | .79 (358) |
| BT4LH | .188 (4.8) | 4.00 (102) | .065 (1.7) | .275 (7.0) | .325 (8.3) | .320 (8.1) | .520 (13.2) | 14.9 (378) | 120 (534) | LIGHT HEAVY | .99 (449) |
| BT5LH | .188 (4.8) | 5.00 (127) | .065 (1.7) | .275 (7.0) | .325 (8.3) | .320 (8.1) | .520 (13.2) | 18.1 (460) | 120 (534) | LIGHT HEAVY | 1.19 (540) |
| BT6LH | .188 (4.8) | 6.00 (152) | .065 (1.7) | .275 (7.0) | .325 (8.3) | .320 (8.1) | .520 (13.2) | 21.2 (538) | 120 (534) | LIGHT HEAVY | 1.39 (631) |
| BT7LH | .188 (4.8) | 7.00 (178) | .065 (1.7) | .275 (7.0) | .325 (8.3) | .320 (8.1) | .520 (13.2) | 24.4 (620) | 120 (534) | LIGHT HEAVY | 1.59 (722) |
| BT8LH | .188 (4.8) | 8.00 (203) | .065 (1.7) | .275 (7.0) | .325 (8.3) | .320 (8.1) | .520 (13.2) | 27.5 (699) | 120 (534) | LIGHT HEAVY | 1.79 (813) |
| BT9LH | .188 (4.8) | 9.00 (229) | .065 (1.7) | .275 (7.0) | .325 (8.3) | .320 (8.1) | .520 (13.2) | 30.7 (780) | 120 (534) | LIGHT HEAVY | 1.99 (904) |

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

PANDUIT CORP. TINLEY PARK, ILLINOIS
DOME-TOP Barb Ty CABLE TIES
BT SERIES

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ±.10(2.5) (.XXX) ±.020(.51)
(.XX) ±.02(.5) ANGLES ±

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY
PMH

MAT'L:

SCALE NONE

6 5/2/06 JABC

REMOVED CURVED TIP REFERENCE &
TIP STYLE COLUMN

BT-0037 6

DATE
6-24-93

NYLON 6.6

DRAWING NO.

BT-0037

SHT. 3 OF 3

DWG
A
SIZE

REV DATE BY CHK

DESCRIPTION

ECN - R CUST SUP

CHK'D
JVL

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[BT6LH-C](#) [BT5LH-C0](#) [BT6LH-C0](#) [BT5LH-C](#) [BT2LH-TL](#) [BT2LH-TL0](#) [BT3LH-TL](#) [BT4LH-TL](#) [BT4LH-TL0](#) [BT7LH-C](#)
[BT7LH-C0](#) [BT8LH-C](#) [BT8LH-C0](#) [BT9LH-C](#) [BT9LH-C0](#) [BT2LH-TL300](#) [BT5LH-C300](#) [BT9LH-C300](#) [BT4LH-TL300](#)
[BT6LH-C300](#) [BT3LH-TL0](#) [BT6LH-C69](#) [BT4LH-TL69](#) [BT8LH-C300](#)