

Datasheet

Stock No: 283-4035

# RS Pro Line Mounting Hydraulic Flow Control Valve 204012, G 1/2, 210 bar



## Product Details

### Brass Flow Control Valves

Manufactured from nickel plated brass these needle operated control valves are available in two options.

Double acting valve is designed to control and shut off the flow

Single acting valve allows flow control with free reverse flow

Nitrile rubber seals

### Flow Control Valves

Single acting and double acting in-line flow control valves. Single acting valves allow flow control in one direction and free flow in the opposite direction. Double acting valves allow flow control in both directions.



## Specifications

Manufacturer Series	FT1251/5
Connection Port Thread	G 1/2
Maximum Flow Rate	50L/min
Body Material	Nickel Plated Brass
Seal Material	Nitrile Rubber
Maximum Operating Pressure	210 bar
Thread Size	1/2 in
Thread Standard	G
Maximum Operating Temperature	+100°C
Minimum Operating Temperature	-20°C