



Rev	AWO #	Description	Date	Appr
-		RELEASED	4/13/06	
A		PART REVISION	4/19/06	
B		ADDED DIM.	3/18/15	AV/RT

APPROVED: _____
 DATE: _____ TITLE: _____



Positions: 2 thru 20
 A = .098 [2.50] x No. of Spaces
 B = .098 [2.50] x No. of Spaces + .125 [3.20]
 C = .098 [2.50] x No. of Spaces + .189 [4.80]

SPECIFICATIONS:
 Material: _____
 Contact: Brass
 Insulator: Nylon 66 UL 94V-O, White
 Plating: _____
 Tin over Copper underplate overall
 Electrical:
 Operating voltage: 250 VAC max
 Current rating: 2 Amp max
 Contact Resistance: 20M ohms max
 Withstanding Voltage: 1,000V AC/MINUTE
 Insulation resistance: 1,000Mohms min.
 Temperature Rating:
 Operating temperature: -25°C to +85°C
 Environmental:
 Lead free, RoHS compliant



ADAM TECH

909 Rahway Avenue, Union, NJ 07083
 Phone: 908-687-5000 Fax: 908-687-5710

WIRE TO BOARD PITCH: 2.5MM
 CRIMP HOUSING STRAIGHT TYPE

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM]		TOLERANCES: EXCEPT AS NOTED	
.X	± .10	ØXX	± .10
.XX	± .020	ØXXX	± .015
.XXX	± .015	ØXXXX	± .010
APPROVALS		DATE	
DRAWN	LJU	4/13/06	
CHECKED			
APPROVED			
REF:	SIZE	PART NO.	REV.
	X	25CH-B-XX	B
SCALE:	NTS	SHEET	1 OF 1