



REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED
A	NEW RELEASE	LJH 06/22/05'		



N: HALF OF PIN POSITIONS
H: CUSTOMER LENGTH AVAILABLE



RECOMMEND PCB LAYOUT(TOLERANCE=±0.05)

NOTES:

- ELECTRICAL CHARACTERISTICS:
 - CONTACT RESISTANCE: 20mΩ Max. INITIAL.
 - DIELECTRIC WITHSTANDING VOLTAGE: 500V AC(rms) FOR 1 MINUTE.
 - INSULATION RESISTANCE: 1000 MΩ Min.
- ENVIRONMENT CHARACTERISTICS:
 - OPERATING TEMPERATURE: 0°C~+85°C.
 - STORAGE TEMPERATURE: -20°C~+70°C.
- PART NUMBER: DS1026-06

4. PRODUCT NUMBER CODE:

DS1026-06 - X X X X X

- CONTACTS TYPE
V:VERTICAL
- HOUSING COLOR
B:BLACK
- CONTACT PLATING
8: FULL GOLD FLASH
- CONNECTOR TYPE
S:SOCKET
- No.OF CONTACTS
2*1-2*X
- SERIES No.
DS1026-06

Tel: 86-574-63508787

Fax: 86-574-63510817

E-mail: zheng@cnconfly.com.cn

Http://www.cnconfly.com.cn

West China Ningbo China
晨翔电子有限公司
CONNFLY CONNFLY ELECTRONIC CO. LTD

GENERAL TOLERANCE		ANGLE TOLERANCE		PROJECTION	TITLE
X.	±0.60	X.	±5°		DUAL ROW RIGHT ANGLE
.X	±0.38	.X	±3°	mm	
.XX	±0.25	.XX	±2°		
DRAWING TYPE				SHEET	SERIES
CUSTOMER				1 OF 1	DS1026-06 SERIES
SCALE				SHEET SIZE	
1:1				A4	
DRAWING NO.				C-DS1026-06-XXXXX	

ITEM	PART NAME	PART NO.	MATERILAS	FINISHED
2	CONTACT		COPPER ALLOY	GOLD PLATED
1	HOUSING		THERMOPLASTIC	UL 94 V-0