


■ SPECIFICATIONS

- Voltage rating: 250V AC, DC
- Current rating: 1A, AC, DC (AWG#28)
- Withstanding voltage: 500V AC/minute
- Insulation resistance: 100MΩ min
- Temperature range: -40°C - +85°C
- Contact resistance: 20mΩ max

■ HOUSING

- Part No. :SCT1251H-XX
- Poles:2-16
- Material:Nylon 66 UL94V-0
- Q' TY: 1,000 pcs/bag



NO	PART NO	DIMENSION (mm)		
		A	B	C
1	SCT1251H-02	1.25	4.25	2.95
2	SCT1251H-03	2.50	5.50	4.20
3	SCT1251H-04	3.75	6.75	5.45
4	SCT1251H-05	5.00	8.00	6.70
5	SCT1251H-06	6.25	9.25	7.95
6	SCT1251H-07	7.50	10.50	9.20
7	SCT1251H-08	8.75	11.75	10.45
8	SCT1251H-09	10.00	13.00	11.70

NO	PART NO	DIMENSION (mm)		
		A	B	C
9	SCT1251H-10	11.25	14.25	12.95
10	SCT1251H-11	12.50	15.50	14.20
11	SCT1251H-12	13.75	16.75	15.45
12	SCT1251H-13	15.00	18.00	16.70
13	SCT1251H-14	16.25	19.25	17.95
14	SCT1251H-15	17.50	20.50	19.20
15	SCT1251H-16	18.75	21.75	20.45

					OPERATION	DRAW	Micky.Liu	2006/05/02	SCALE		森康达电子有限公司 SCONDAR ELECTRONIC LIMITED
					~ 10	±0.15			UNIT	mm	
					20 ~ 30	±0.30			SIZE	A4	
					30 ~	±0.50			SHEET	1/1	
					Angle	± 2'			TITLE:	MX1.25 HOUSING	
0	05/12/27								PART NO.	SCT1251H-XX	
REV	DATE	MODIFICATION DESCRIPTION	CHANGE	APPROVE	APPROVE	Hellen.Li	2006/05/02	PROJ.	DRAWING NO.	SCT1251	