

1 2 3 4 5 6 7 8 9 10

A

B

C

D

E

F

G

H

A

B

C



D

E

F

G

H






SPECIFICATIONS

Voltage rating: 125V AC, DC
 Current rating: 1A, AC, DC (AWG#28)
 Withstanding voltage: 500V AC/minute
 Insulation resistance: 100M Ω min
 Temperature range: -40°C - +85°C
 Contact resistance: 20m Ω max

TERMINAL

Part No.: SCT1251TPB
 Thickness: 0.15mm
 Material: Phosphorus copper tin plating
 Wire Range: AWG#28-#32 (OD1.0mm)
 Reel Q' ty: 15,000pcs



					OPERATION	DRAW	Judy.Huang	2014/09/17	SCALE		森康达电子有限公司 SCONDAR ELECTRONIC LIMITED	
					~ 10 ±0.15	DESIGN			UNIT	mm		PART NO.
					20 ~ 30 ±0.30	CHECK	Micky.Liu	2014/09/17	SIZE	A4	TITLE:	MX1.25 TERMINAL
0	05/12/27		NEW		30 ~ ±0.50	APPROVE	Hellen.Li	2014/09/17	SHEET	1/1	DRAWING NO.	SCT1251
REV	DATE		MODIFICATION DESCRIPTION	CHANGE	APPROVE				PROJ.	◆ ←		

1 2 3 4 5 6 7 8 9 10