



| PANDUIT PART NO. | BUNDLE DIA. | | A | B | C | D | E | F | G | H | J | MAX. PANEL THICKNESS in (mm) | MIN. LOOP TENSILE lbs (N) | CROSS SECTION | WEIGHT 100 pcs lbs (g) |
|------------------|-----------------|-----------------|---------------|---------------|---------------|---------------|---------------|--------------|---------------|---------------|----------------|---------------------------------|------------------------------|---------------|------------------------------|
| | MIN. in (mm) | MAX. in (mm) | | | | | | | | | | | | | |
| PLWP1SB | .06 (1.5) | 1.0 (25.4) | .052 (1.3) | .190 (4.8) | .230 (5.8) | .370 (9.4) | .320 (8.1) | 5.2 (132) | .260 (6.6) | .187 (4.7) | .593 (15.1) | .157 (4.0) | 50 (222) | STANDARD | .29 (132) |
| PLWP2SB | .06 (1.5) | 1.75 (44.5) | .052 (1.3) | .190 (4.8) | .230 (5.8) | .370 (9.4) | .320 (8.1) | 7.8 (198) | .260 (6.6) | .187 (4.7) | .593 (15.1) | .157 (4.0) | 50 (222) | STANDARD | .37 (168) |

NOTE: SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE, MATERIAL AND PART COLOR.

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

PANDUIT CORP. TINLEY PARK, ILLINOIS

LOCKING WING PUSH MOUNT TIE
PLWP1SB & 2SB

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) $\pm .1(2.5)$ (.XXX) $\pm .020(.51)$
(.XX) $\pm .02(.51)$ ANGLES \pm -----

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY
KJL

MAT'L:

SCALE NONE

6 1/19/04 JABO CHANGED FORMAT FOR CONSISTENCY
SEE ECN FOR DETAILS

23526 6

DATE
11/23/88

SEE NOTE

DRAWING NO.
SS-23526

DWG
A
SIZE

| REV | DATE | BY | CHK | DESCRIPTION | ECN - R | CUST | SUP | CHK'D HVP |
|-----|---------|------|-----|---|---------|------|-----|--------------|
| 6 | 1/19/04 | JABO | | CHANGED FORMAT FOR CONSISTENCY SEE ECN FOR DETAILS | 23526 | 6 | | |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[PLWP2SB-D](#)