

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200980160](#)
Status: **Active**
Overview: Brad Micro-Change (M12) Connectors
Description: Micro-Change (M12) Double-Ended Cordset, 5 Poles, Female (Straight) to Male (Straight), 24 AWG, 15.0m (49.21') Length, PROFIBUS PUR Cable Preferred Version in Europe

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Industrial Cordsets
Series	120098
Connector End A	Micro-Change (M12)
Connector End B	Micro-Change (M12)
IP Rating	IP67
Material - Contact	Copper Alloy
Overview	Brad Micro-Change (M12) Connectors
Product Name	Micro-Change (M12)
Protocol	EtherNet
Region	America, Asia, Europe
Type	Double Ended
UPC	78172500036

Physical


Cable Diameter	8.00mm (.315")
Cable Length	15.0m (49.21')
Color - Cable Jacket	Purple
Coupling Style	Threaded
Gender	Female-Male
Keyway	Reverse
LED Indicator	No
Material - Cable Jacket	PUR
Material - Connector Body	PUR
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Orientation	Straight to Straight
Poles	5
Temperature Range - Operating	-20°C to +80°C
Wire Size AWG	24
Wire/Cable Type	Twisted Pair

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	60V AC/DC

Material Info

Engineering Number	BB5S30PP4M150
--------------------	---------------



EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[120098 Series](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1200980160](#)