




FACE VIEW-FEMALE INSERT
A-CODE



- 1 BROWN
- 2 WHITE
- 3 BLUE
- 4 BLACK



W04001A09MXXX

CABLE TYPE
4x22AWG
PVC YELLOW

CABLE LENGTH
003----0.3 METER
010----1 METER
100----10 METER

SPECIFICATIONS:

ULTRA LOCK FEMALE:
 COUPLING NUT MATERIAL: NICKEL PLATED BRASS
 CONTACT MATERIAL: GOLD/NICKEL OVER COPPER ALLOY
 INSERT MATERIAL: BLACK PUR
 O-RING: GREEN FPM
 OVERMOLD: YELLOW PUR

CABLE: #22/4 YELLOW PVC JACKET, 105°C 300V
 CABLE MARKING: RU AWM 2661 22 AWG/4C 105°C 300V (UL FILE NUMBER) CSA
 AWM I/II A/B 80°C 300V FT1
 ASSEMBLY RATINGS: 250V Max., 4A Max.
 PACKAGING: CABLE ASSEMBLIES ARE BAGGED SEPARATELY IN POLY BAGS
 WITH BAR CODE LABEL ATTACHED TO OUTSIDE OF BAG

CORRECTED WIRE STRIP EC NO: IPG2014-1957 DRWN: RSTONE CHKD: B ARDEN APPR: BWOODMAN 5/12/14	DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION		
			mm	INCH	IN/MM		NTS	INCH	TITLE MICRO CHANGE ULTRA LOCK 4-POLE FEMALE 90 DEGREE #22/4 PVC CABLE		
			4 PLACES	±---	±---	DRAWN BY	DATE	MATERIAL NO.			
			3 PLACES	±---	±.005	TWOLDEG	2009/07/06	---		SHEET NO.	
2 PLACES	±0.13	±.010	APPROVED BY		DATE	---		1 OF 1			
1 PLACE	±0.25	±.020	ANGULAR ±1/2°		---		MATERIAL NO.		---		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SIZE		B		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				

F

E

D

C

B

A

F

E

D

C

B

A

10

9

8

7

6

5

4

3

2

1

10

9

8

7

6

5

4

3

2

1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1200790232](#)