

REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED
A	NEW RELEASE	LJH 09/22/05'		

NOTES:



- ELECTRICAL CHARACTERISTICS:
  - CONTACT RESISTANCE: 20mΩ Max. INITIAL.
  - DIELECTRIC WITHSTANDING VOLTAGE: 500V AC(rms) FOR 1 MINUTE.
  - INSULATION RESISTANCE: 1000MΩ Min.
- ENVIRONMENT CHARACTERISTICS:
  - OPERATING TEMPERATURE: 0°C~+85°C.
  - STORAGE TEMPERATURE: -20°C~+70°C.

3. PART NUMBER: DS1026-01


4. PRODUCT NUMBER CODE:

DS1026-01 - X X X X X

CONTACTS TYPE  
V:VERTICAL TYPE  
HOUSING COLOR  
B:BLACK  
CONTACT PLATING  
8: FULL GOLD FLASH  
CONNECTOR TYPE  
S:SOCKET  
No.OF CONTACTS  
1\*1-1\*X  
SERIES No.  
DS1026-01



N:NUMBER OF CONTACTS



RECOMMEND PCB LAYOUT(TOLERANCE= $\pm 0.05$ )

Tel: 86-574-63508787

Fax: 86-574-63510817

GENERAL TOLERANCE		ANGLE TOLERANCE		PROJECTION	TITLE
X.	$\pm 0.60$	X.	$\pm 5^\circ$		FEMALE HEADER PITCH 2.0mm TYPE
.X	$\pm 0.38$	.X	$\pm 3^\circ$	UNITS	mm
.XX	$\pm 0.25$	.XX	$\pm 2^\circ$	SHEET SIZE	A4
				SERIES	DS1026-01 SERIES

ITEM	PART NAME	PART NO.	MATERIALS	FINISHED	DRAWING NO.	CUSTOMER
2	CONTACT		COPPER ALLOY	GOLD FLASH		
1	HOUSING		THERMOPLASTIC	UL 94 V-0		
					SCALE	1:1 SHEET 1 OF 1
					DRAWING NO.	C-DS1026-01-XXXXX

晨翔电子有限公司  
CONNFLY CONNFLY ELECTRONIC CO. LTD