



REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED
A	NEW RELEASE	LJH 06/21/05'		
B	ADD DIM	LL 10/30/06'		
C	ADD DIM	LL 11/28/06'		



A&B: CUSTOMER LENGTH AVAILABLE  
N: HALF OF CONTACTS



RECOMMEND PCB LAYOUT (TOLERANCE = ±0.05)

NOTES:

- MATERIAL & FINISHES
  - INSULATOR: THERMOPLASTIC (UL 94V-0).
  - CONTACT MATERIAL: COPPER ALLOY.
- SPECIFICATION
  - CURRENT RATING: 1.5 Amp.
  - INSULATION RESISTANCE: 1000MΩ Min.
  - DIELECTRIC WITHSTANDING: 600VAC.
  - CONTACT RESISTANCE: 20mΩ Max.
  - OPERATING TEMPERATURE: -20°C TO +80°C.
- PART NUMBER: DS1025-05
- PRODUCT NUMBER CODE:  
DS1025-05 - X X X X X X

TABLE A:

TYPE	Dimension	
	A	B
1	2.80	4.00
2	3.50	5.08
3	10.00	2.00
4	2.80	10.20
5	4.00	8.00
6	2.50	4.30
7	2.80	3.90
8		

TABLE A & DIM. A B TYPE

1: TYPE 1  
7: TYPE 7

CONTACTS TYPE  
V: VERTICAL TYPE  
HOUSING COLOR  
B: BLACK

CONTACT PLATING  
8: FULL GOLD FLASH  
6: TIN  
CONNECTOR TYPE  
P: PLUG

No. OF CONTACTS  
2\*2-2\*X

SERIES No.  
DS1025-05

GENERAL TOLERANCE		ANGLE TOLERANCE	
X.	±0.60	X.	±5°
.X	±0.38	.X	±3°
.XX	±0.25	.XX	±2°

PROJECTION	TITLE	DUAL ROW STRAIGHT	
UNITS	mm		
SHEET SIZE	A4	SERIES	DS1025-05 SERIES

2	CONTACT		COPPER ALLOY		GOLD PLATED	DRAWING TYPE	CUSTOMER
1	HOUSING		THERMOPLASTIC		UL 94 V-0	SCALE	1:1 SHEET 1 OF 1
ITEM	PART NAME	PART NO.	MATERIALS		FINISHED	DRAWING NO.	C-DS1025-05-XXXXX



晨翔电子有限公司

CONNFLY CONNFLY ELECTRONIC CO. LTD