



Insulated Female Disconnects

159-2211, 159-2187, 159-2205, 159-2251



Insulated Female Disconnects

Dimensions: In.
(Except Where Noted)



SPECIFICATIONS	
Wire range:	22 - 16 AWG (1.25mm ²)
Maximum electric current:	10A
Maximum electrical rating:	300V max. @ 75°C
Insulation color:	red
Terminal material:	brass
Insulation material:	vinyl
Double crimp:	sleeve on barrel
Barrel dimension:	B = .197 (5.0mm)
	C = .067 (1.7mm)
	D = .106 (2.7mm)

Mouser Stock No.	NEMA Tab (In.)	Material Thickness (In.)	Dimensions (In.)			
			W	F	P	L
159-2187	.020 x .187	.014	.220	.256	.551	.748
159-2205	.020 x .205	.014	.256	.248	.622	.787
159-2211	.020 x .110	.012	.150	.252	.551	.748
159-2251	.032 x .250	.016	.291	.311	.669	.827

Date Last Revised: 10-18-05

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC-300733

159-2211, 159-2187, 159-2205, 159-2251

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[159-2187](#) [159-2205](#) [159-2211](#) [159-2251](#)