




APPROVED: \_\_\_\_\_  
 DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

Rev	AWO #	Description	Date	Appr
-		RELEASED	01/17/07	
A		UPDATED SPECIFICATIONS	7/28/09	
B		REVISED SHAPE	3/23/11	



**SPECIFICATIONS:**

**Material:**  
 Insulator: Nylon 66, rated UL 94V-0  
 Insulator color: Natural  
 Contacts: Phosphor Bronze  
**Plating:**  
 Tin over Nickel underplate overall  
**Electrical:**  
 Operating voltage: 50 VAC max  
 Current rating: 1 Amps max  
 Contact resistance: 20 mohms max  
 Insulation resistance: 500 Mohms min  
 Dielectric withstanding voltage: 500 VAC for 1 minute  
**Temperature Rating:**  
 Operating temperature: -25°C to +85°C  
 Environmental:  
 Lead free, RoHS compliant.

Positions: 02 thru 15  
 A = .059 [1.50] X No. of Spaces.  
 B = .059 [1.50] X No. of Spaces + .118 [3.00].  
 C = .059 [1.50] X No. of Spaces + .075 [1.90].

UNLESS OTHERWISE SPECIFIED  
 ALL DIMENSIONS ARE INCHES [MM]  
 TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X ± .10	ØX ± .10
.XX ± .020	ØXX ± .015
.XXX ± .015	ØXXX ± .010

APPROVALS	DATE
DRAWN	BW
CHECKED	
APPROVED	

**ADAM TECH**  
 909 Rahway Avenue, Union, NJ 07083  
 Phone: 908-687-5000 Fax: 908-687-5710

TITLE	ZH 1.50mm HOUSING
SIZE	PART NO.
X	15CH-A-XX
REF:	S00124T
SCALE:	NTS
SHEET	1 OF 1
REV.	B

