ZS25-PE



TE Connectivity has acquired the DIN Rail Terminal Block product range from ABB

Products + Low Voltage Products and Systems + Connection Devices + Terminal Blocks + SNK Series

General Information

Extended Product Type: ZS25-PE

Product ID: 1SNK512150R0000 EAN: 3472595121502

Catalog Description: ZS25-PE Screw Clamp Terminal Block - Ground - Green/Yellow

Long Description: Improve the safety of your installation in the event of a short-circuit thanks

to our screwless rail contact: - rail contact non operator dependent, secure d snap on or off the rail, - Same profile as ZS25 for aligned marking and id

entical end section.

Ordering

Color: Green-Yellow

Minimum Order Quantity: 20 piece

Customs Tariff Number: 85369010

Popular Downloads

Data Sheet, Technical Information: 1SNK161069D0201

Instructions and Manuals: 1SNK160027C0201

Dimensions

Product Net Width: 12 mm

Product Net Height: 63.6 mm

Product Net Length: 48.9 mm

Product Net Depth / Length: 48.9 mm

Product Net Weight: 38 g

Technical

Rated Cross-Section: 16 mm²

Spacing: 12 mm

Connection Type: Screw clamp

1

Function: Ground

Number of Levels:

Connecting Capacity Main Circuit:	Screw Clamp / Flexible 1x 0.5 25 mm ² Screw Clamp / Flexible 2x 0.5 10 mm ² Screw Clamp / Rigid 1x 0.5 25 mm ² Screw Clamp / Rigid 2x 0.5 10 mm ² Screw Clamp / With Insulated Ferrule 1x 0.5 16 mm ² Screw Clamp / Without Insulated Ferrule 1x 0.5 16 mm ² Screw Clamp / With Twin Ferrule 2x 0.5 10 mm ²
Gauge Type:	A6-B6
Rated Short-time Withstand Current (I _{cw}):	for 1 s 1920 A
Rated Impulse Withstand Voltage (U _{imp}):	8000 V
Dielectric Test Voltage:	2200 V
Pollution Degree:	3
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Insulation Material:	Polyamide
Mounting on DIN Rail:	TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Wire Stripping Length:	13.5 mm
Technical UL/CSA	
Connecting Capacity Main Circuit UL/CSA:	Screw Clamp / Rigid 1x 24 3 AWG Screw Clamp / Rigid 2x 20 10 AWG Screw Clamp / With Insulated Ferrrule 1x 24 8 AWG Screw Clamp / Without Insulated Ferrule 1x 24 4 AWG Screw Clamp / With Twin Ferrule 2x 20 10 AWG
Connecting Capacity UL/CSA:	Stranded 3 AWG
Flammability According to UL94:	V0
Environmental	
Ambient Air Temperature:	Operation -55 +110 °C Storage -55 +110 °C
Resistance to Vibrations acc. to IEC 60068-2-6:	Compliant
RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment
Certificates and Declarations ([Document Number)
ATEX Certificate:	1SND162004A1708
BV Certificate:	1SND161073A0204
CB Certificate:	1SND161101A0200
CSA Certificate:	1SND161070A0209
cUL Certificate:	1SND161041A0210

1SND225112U1004

Declaration of Conformity - CE:

DNV Certificate:	1SND161087A0202
EAC Certificate:	1SND161010A1100
Environmental Information:	1SND220170E0200
Instructions and Manuals:	1SNK160027C0201
RMRS Certificate:	1SND161008A1101
RoHS Information:	1SND230491F0206

Classifications

Object Classification Code: X

ETIM 4: EC000901 - Ground terminal block

ETIM 5: EC000901 - Ground terminal block

ETIM 6: EC000901 - Ground terminal block

Container Information

Package Level 1 Units: 20 piece Package Level 1 Width: 62 mm Package Level 1 Depth / Length: 252 mm Package Level 1 Height: 52 mm Package Level 1 Gross Weight: 0.78 kg Package Level 1 EAN: 3472595121502 Package Level 2 Units: 300 piece Package Level 2 Width: 300 mm Package Level 2 Depth / Length: 400 mm Package Level 2 Height: 200 mm Package Level 2 Gross Weight: 11.7 kg Package Level 3 Units: 14400 piece **Product Packing Type:** Box

