



Spring Contact SCTA_A Series (Standard Type)

Dimensions (W × D)	1.4 × 1.4mm
Height in use	0.8 to 1.2mm
Travel	0.6mm
Mounting type	Surface mounting type
Mounting style	Standard mount
Packing system	Taping
Minimum order unit (pcs.)	13,000
Operating temprature range	−30°C to +85°C
Rated current	3A
Contact resistance (Initial)	Connector contacts $40 \text{m}\Omega$ max.
Stroke Frequency	500 times


Dimensions



Land Dimensions




Packing Specifications



Export package measurements (mm)		403 × 403 × 167
Tape width (mm)		8
	1 case / export packing	g 78,000
	1 case / Japan	39,000
Number of packages (pcs.)	1 reel	13,000

Soldering Conditions



Temperature on the surface of PWB

Notes are common to this series/models.

- 1. This site catalog shows only outline specifications. When using the products, please obtain formal specifications for supply.
 2. Please place purchase orders per minimum order unit (integer).