



BUTT CONNECTORS B型中間套管

TERMINAL MATERIAL : COPPER TUBE



Manufactured from soft drawn pure copper tube to JIS-H3300, C 1020T-0 (Oxygen-Free Copper) which gives the best properties possible.

A complete range butt connectors, ranging from 1.25mm to 325mm.

ITEM NO.	DIMENSIONS			WIRE RANGE		
	L	D φ	d φ	Single mm	Twine mm ²	AWG
B-1.25	16.5	3.3	1.9	0.57-1.44	0.25-1.65	22-16
B-2	16.5	4.0	2.6	1.44-1.82	1.04-2.63	16-14
B-3.5	16.5	5.0	3.6	1.82-2.89	1.65-4.17	14-12
B-5.5	16.5	5.5	3.7	1.82-2.89	2.63-6.64	12-10
B-8	22.5	7.1	5.1	2.89-3.65	6.64-10.52	8
B-14	27.5	9.0	6.4	3.65-4.62	10.52-16.78	6
B-22	30.5	11.4	8.2	4.62-5.81	16.78-26.66	4
B-38	33.5	13.3	10.1	5.81-7.34	26.66-42.42	2
D-60	36.0	15.4	12.0	7.34-9.27	42.42-60.57	1/0
B-70	37.8	17.4	14.0	8.26-9.27	60.57-76.28	2/0
B-80	39.5	19.4	15.4	9.27-10.41	76.28-96.3	3/0
B-100	39.5	22.0	17.6	10.41-11.68	96.3-117.2	4/0
B-125	43.4	24.1	19.2	10.01-12.7	107.2-130.4	4/0
B-150	55.5	26.0	20.9	11.68-13.8	117-152.05	250-300MCM
B-180	58.5	28.6	22.0	13.8-15.6	152.05-192.6	300-350MCM
B-200	64.5	32.5	25.7	15.6-17.5	192.6-242.2	400MCM
B-250	64.5	32.5	25.7	15.6-17.5	192.6-242.2	400MCM
B-325	73.5	37.0	29.0	17.5-20.3	242.27-325	500-600MCM

INSULATED BUTT CONNECTORS 絕緣中間套管

TERMINAL MATERIAL : COPPER INSULATION MATERIAL : VINYL&NYLON



ITEM NO.	DIMENSIONS				WIRE RANGE			COLOR
	d φ	D φ	L	ℓ	Single mm	Twine mm ²	AWG	
BF1.25LP	1.8	4.0	22.7	15.0	0.57-1.44	0.75-1.25	22-16	RED
BF2LP	2.3	4.5	22.7	15.0	1.44-1.82	1.25-2.0	16-14	BLUE
BF5.5LP	3.5	6.8	26.7	15.0	1.82-2.98	2.64-6.64	12-10	YELLOW
BF1.25	1.8	4.0	22.7	15.0	0.57-1.44	0.75-1.25	22-16	RED
BF2	2.3	4.5	22.7	15.0	1.44-1.82	1.25-2.0	16-14	BLUE
BF5.5	3.5	6.8	26.7	15.0	1.82-2.98	2.64-6.64	12-10	YELLOW
BF8	5.1	8.5	35.8	19.2	2.89-3.65	6.64-10.52	8	RED

