

Capacity	kg	40-50	
Comprehensive Error	mv/v	0.05	
Output Sensitivity	mv/v	1.0±0.1	
Nonlinearity	%FS	0.03	
Repeatability	%FS	0.03	
Hysteresis	%FS	0.03	
Creep	(3min)%FS	0.03	
Zero Drift	(1min)%FS	0.03	
Temp. Effect on Zero	%FS/10°C	1	
Temp. Effect on Output	%FS/10°C	0.05	
Zero Output	mV/V	±0.1	
Input Resistance	Ω	1000±20	
Output Resistance	Ω	1000±20	
Insulation Resistance	MΩ	≥5000	
Excitation Voltage	V	≤10	
Operation Temp. Range	°C	0--+50	
Overload Capacity	%FS	150	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[SparkFun Electronics:](#)

[SEN-10245](#)