



APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	6/13/14	
A		UPDATE SPEC.	8/27/15	AY



SPECIFICATIONS:

- Material: Insulator: PA66, rated UL 94V-0
- Insulator color: Green
- Screw: M2, Steel, Zinc plated
- Wire Guard: Brass, Nickel plated
- Clamp: Phosphor Bronze, Nickel plated
- Electrical:
 - Operation voltage: 300V max
 - Current rating: 8 Amps max
 - Contact resistance: 20 mohms max
 - Insulation resistance: 500 Mohms min @ 500 VDC
 - Dielectric withstanding voltage: 2,000 VAC for 1 minute
- Mechanical:
 - Torque: 0.2Nm, 1.7lb-in
 - Strip length: 6-7mm
 - Temperature Rating: Operating temperature: -40°C to +105°C
- Environmental: Lead free, RoHS compliant.

Positions: 2 thru 24
 A = .138 [3.50] x No. of Spaces + .169 [4.30]
 B = .138 [3.50] x No. of Spaces

UNLESS OTHERWISE SPECIFIED
 ALL DIMENSIONS ARE INCHES [MM]
 TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X ± .10	ØXX ± .10
.XX ± .020	ØXXX ± .015
.XXX ± .015	ØXXXX ± .010

ADAM TECH
 909 Rahway Avenue, Union, NJ 07083
 Phone: 908-687-5000 Fax: 908-687-5710

TITLE: **PLUGGABLE BLOCK, PITCH .138 [3.50]**

APPROVALS	DATE	SIZE	PART NO.	REV.
DRAWN AY	6/13/14	X	EBKA-XX-A	A
CHECKED				
APPROVED				

REF: S00067C SCALE: NTS SHEET 1 OF 1

