


NOTE:

MATERIAL		
HOUSING:		PBT UL94V-0, BLACK
CONTACT:		BRASS
NUT:		BRASS
SHELL:		BRASS
O-RING:		NBR, BLACK
FINISH		
CONTACT:		GOLD PLATED OVER 50µ" NICKEL
NUT:		NICKEL PLATED
SHELL:		NICKEL PLATED
ELECTRICAL		
RATED CURRENT:		1A
RATED VOLTAGE:		60V
INSULATION RESISTANCE:		100 mΩhms MIN.
CONTACT RESISTANCE:		10 MΩhms MAX.
WATER PROOF:		IP67
ENVIRONMENT		
OPERATION TEMPERATURE:		-40°C TO +85°C



852-002-213R00Y

1 = GOLD FLASH
4 = 10µ" GOLD

RoHS COMPLIANT

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:	M. SIGMON	DATE:	03-03-16
CHECKED:		DATE:	

NorComp

SCALE:	NTS	SHEET	1	OF	1	REV	1
DWG NO.	852-002-213R00Y						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NorComp:](#)

[852-002-213R001](#)