

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0466261305](#)  
**Status:** **Active**  
**Overview:** [L1NK Connector System](#)  
**Description:** L1NK 250 Female Crimp Terminal, 22-24 AWG, Tin (Sn) Plating, Reel

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Application Specification 2079020001-AS-000 (PDF)</a>
<a href="#">Product Specification 2079020001-PS-000 (PDF)</a>	<a href="#">Packaging Specification PK-46626-001-001 (PDF)</a>
<a href="#">Product Specification 2079020001-PS-CH-000 (PDF)</a>	<a href="#">Test Summary 2079020000-TS-000 (PDF)</a>
<a href="#">Product Specification 2079020001-PS-ES-000 (PDF)</a>	<a href="#">Datasheet (PDF)</a>
<a href="#">Product Specification 2079020001-PS-JP-000 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Product Specification 2079020001-PS-SK-000 (PDF)</a>	

**General**

Product Family	Crimp Terminals
Series	46626
Application	Power, Wire-to-Board
Crimp Quality Equipment	Yes
Overview	<a href="#">L1NK Connector System</a>
Product Name	L1NK 250
UPC	191130122134

**Physical**

Durability (mating cycles max)	25
Gender	Female
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.051/g
Packaging Type	Reel
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.42mm-1.60mm
Wire Size AWG	22, 24
Wire Size mm <sup>2</sup>	0.20-0.33

**Electrical**

Current - Maximum per Contact	6.5A
Voltage - Maximum	250V AC (RMS)/DC

**Material Info**

**Reference - Drawing Numbers**

Application Specification	2079020001-AS-000
Packaging Specification	PK-46626-001-001
Product Specification	2079020001-PS-000, 2079020001-PS-CH-000, 2079020001-PS-ES-000, 2079020001-PS-JP-000, 2079020001-PS-SK-000
Sales Drawing	466260002-SD-000
Test Summary	2079020000-TS-000



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2020)9139-DC (19  
Jan 2021)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[46626 Series](#)

**Use With**

L1NK 250 Receptacle Housing [207841](#)

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

**Description**

**Product #**

Extraction Tool for L1NK 250 Receptacle Crimp Terminals, 22-28 AWG Hand Crimp Tool for L1NK 250 Female Crimp Terminals, 22-28 AWG, UL1007 Wire	<a href="#">2002221000</a>
--	----------------------------

FineAdjust Applicator639047600  
for L1NK 250 Female  
Crimp Terminal,  
22-24 AWG, UL1007  
Wire

This document was generated on 05/07/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[46626-1305](#)