



### FEATURES:

- Cable offers test versatility by including a BNC connector to a high performance SMA and RG316/U cable.
- BNC Connectors feature tarnish resistant bodies and PTFE dielectrics for optimum performance.
- Connector center contacts are gold plated for reliable electrical connection.

### MATERIALS:

BNC: Body: Brass, Nickel Plated

Center Contacts: Brass, Gold Plated (Male)

Dielectric: PTFE

Impedance: 50 Ohms

Cable: RG316/U: Single Shield With 26 AWG Center Cond. (7 x .0067) Silver Coated Copper Covered Steel,

Impedance: 50 Ohms (Nom.), Capacitance: 29.0 pf/ft., Loss (Max): 0.56 dB/ft. @ 3 GHz.,

Jacket: FEP, Color: Tinted Brown, O.D.: 0.098" (2,50 cm)

SMA: Body/Fittings: Stainless Steel, Finish – Passivated Steel

Center Contact: Brass, Gold Plated

Impedance: 50 Ohms Nominal

### RATINGS:

Operating Voltage: 335VRMS Max.

Operation Temperature: +165°C (+329°F) Max.

### ORDERING INFORMATION: Model 4935-BB-XX

XX = Cable Length In Inches

Std. Lengths: 4" (10,16 cm), 6" (15,24 cm), 12" (30,48 cm), 24" (60,96 cm), 36" (91,44 cm), 48" (121,92 cm), 60" (152,4 cm) & 120" (304,8cm).

Additional lengths can be quoted upon requested.

Ordering Example: 4935-BB-60 is a cable with a length of 60" (152,4 cm)

All dimensions are in inches and metric. All specifications are to the latest revisions. Specifications are subject to change without notice.  
Registered trademarks are the property of their respective companies. Made in USA

Sales: 800-490-2361 Fax: 888-403-3360  
Technical Assistance: 800-241-2060

PomonaACCESS 90409 (800) 444-6785 or (425) 446-6010  
More drawings available at [www.pomonaelectronics.com](http://www.pomonaelectronics.com)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[4935-BB-120](#) [4935-BB-60](#) [4935-BB-24](#) [4935-BB-48](#) [EM4935-BB-12](#)