


BU-22731031

(8-Position Right Angle Female Receptacle to Wire Leads, 4.92')





Pîn Out

J 1	COLOR	J2
1	BROWN	
2	WHITE	
3	BLUE	
4	BLACK	
5	GRAY	OPEN
6	PINK	
7	VIOLET	
8	ORANGE	
SHELL	BRAID	

Toll Free: 800.955.2629

Phone: 330.780.2525

Fax: 330.780.2524

• Mueller's BU-22731031 is a shielded cable assembly with an 8-position right angle female receptacle with exposed wire ends.

Shell Size: M12 (A Coding)
Standard: IEC 61076-2-101
Connector Locking System: Screw-locking

• Waterproof Rating: IP67

• Cable Material: Polyurethane

Overall length = 4.92' (1.5m)

Coupling Nut: Anodized Aluminum

• Ratings:

o Current: 2A

Voltage: 30V AC/DC
Temperature: -40°C to 105°C

RoHS 3 Compliant