

Data Sheet | Item Number: 261-307/331-000

2-conductor terminal block; on one side with push-button; with fixing flange; 1-pole;
for screw or similar mounting types; Fixing hole 3.2 mm Ø; 2.5 mm²; CAGE CLAMP®;
2,50 mm²; green-yellow



<https://www.wago.com/261-307/331-000>



Color:  green-yellow

Similar to illustration



Similar to illustration

Connection data

Connection points	2
Total number of potentials	1
Number of levels	1

Connection 1

Connection technology	CAGE CLAMP®
Actuation type	Operating tool
Connectable conductor materials	Copper
Solid conductor	0.08 ... 2.5 mm ² / 28 ... 14 AWG
Fine-stranded conductor	0.08 ... 2.5 mm ² / 28 ... 14 AWG
Strip length	8 ... 9 mm / 0.31 ... 0.35 inches
Pole number	1
Wiring direction	Side-entry wiring

Connection 2

Actuation type 2	Push-button
------------------	-------------

Physical data

Width	6 mm / 0.236 inches
Height from the surface	23.3 mm / 0.917 inches
Depth	28.1 mm / 1.106 inches

Mechanical Data

Design	horizontal type
Mounting type	Mounting flange
Marking level	Side marking

Material Data

Note (material data)

[Information on material specifications can be found here](#)

Color green-yellow

Material group I

Insulation material Polyamide (PA66)

Flammability class per UL94 V0

Fire load 0.054 MJ

Halogen-free Yes

Weight 2.3 g

Environmental requirements

Processing temperature -35 ... +85 °C

Continuous operating temperature -60 ... +105 °C

Commercial data

eCl@ss 10.0 27-14-11-06

eCl@ss 9.0 27-14-11-06

ETIM 8.0 EC001284

ETIM 7.0 EC001284

PU (SPU) 200 (50) pcs

Packaging type Box

Country of origin DE

GTIN 4044918622868

Customs tariff number 85369010000

1 Compatible Products

1.1 Required Accessories

1.1.1 End plate

1.1.1.1 End plate

**Item No.: 261-361**

End plate; with fixing flange; gray