



Panel Thickness :  
2.5mm Max.

SPECIFICATION

- 1. Rating : AC 125V 3A Max.
- 2. Contact R. : 50mΩ Max.
- 3. Insulation R. : DC 500V 100MΩ Min.
- 4. Dielectric Strength : AC 1500V 1 minute.
- 5. Operating Temperature : -40℃ ~ +65℃
- 6. Electrical Life : 20,000 make-and-break cycles at full load.
- 7. Mechanical Life : 50,000 make-and-break cycles

30-10060: Open and close type  
30-10061、3010062: Open type

Part No.	Type	Action			Actuator
30-10060	SPST	OFF	-	ON	Black Nylon
30-10061	SPST	OFF	-	(ON)	Black Nylon
30-10062	SPST	OFF	-	(ON)	Red Nylon

品號	30-1006x	件號		圖號	
品名	PUSH-BUTTON SW.	零件		單位	m/m
材質		處理		比例	2:1
修改日期	說明事項	版次	0	審核	設計
				製圖	LIU
				日期	AUG.31.2001
				公差	±0.4