

## Coaxial Cable Connector 24\_TNC-50-2-31/133\_N

### Description

Straight bulkhead cable feed through

Interface standards

IEC 60169-17\_MIL-STD-348A/313\_CECC 22200



### Technical Data

#### Electrical Data

Impedance	50 Ω
Interface frequency max.	11 GHz
Frequency range	DC to 2.5 GHz
Return loss	35 dB

#### Mechanical Data

Centre contact	soldered
Outer contact	soldered
Weight	0.0183 kg

#### Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Gasket	VMQ (Silicone rubber)	
Fastening nut	Brass	SUCOPLATE (R) Plating
Washer	Bronze	SUCOPLATE (R) Plating

### Related Documents

Outline drawing	DOU-00008845
Catalogue drawing	DCA-00008847
Assembly instruction	DOC-0000185023
Mounting hole	DOU-00008751

### Ordering Information

Single package	24_TNC-50-2-31/133_NE
----------------	-----------------------

### Additional Information

Suitable cables	EZ_86_TP_M17, MULTIFLEX_86, SUCOFORM_86
-----------------	---

### Remarks

El. optimized for cable EZ\_86