


## Deep groove ball bearings, single row, shield on both sides

Principal dimensions			Basic load ratings		Fatigue load limit $P_u$	Speed ratings		Mass	Designation
d	D	B	dynamic	static		Reference speed	Limiting speed		
mm			kN		kN	r/min		kg	-
50	90	20	37,1	23,2	0,98	15000	8000	0,46	6210-2Z *



### Calculation factors

$k_r$  0,025

$f_0$  14